

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301050057](#)
Status: **Active**
Overview: Specialty Lighting
Description: Watertite Wet Location 30W 12V Spotlight with Screw Release Guard, 14/2 SOOW, Overall Length 15.24m (50.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA E59049
 UL E59049

General

Product Family Portable Lighting
 Series [130105](#)
 NEMA Configuration Non-NEMA
 Outlet None
 Overview [Specialty Lighting](#)
 Product Name Watertite
 Type Hand Lamps, Specialty Light
 UPC 78678862521

Physical

Cord Length - Primary 15.24m (50.0')
 Cord Length - Secondary N/A
 Depth 120.65mm (4.750")
 Duty Wet Location
 Guard Included Yes
 Guard Type Screw Release
 Height 457.20mm (18.000")
 Length N/A
 Material - Guard #10 Gauge Vinyl Coated Steel
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Quartz Halogen
 Cord Type - Secondary 14/2 SOOW
 Lamp Type PAR36
 Lamp Wattage - Maximum 30W
 Lumens 300
 On/Off Switch No
 Voltage (Fixture) - Maximum 12V AC/DC

Material Info

Engineering Number 1647-12



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130105 Series](#)