






Plastic Boxes

Potting Boxes Style A



These economical, small and light weight plastic enclosures are well suited for all types of applications requiring complete sealing of component parts with potting compounds.

Design Features

- Available in 3 styles and a variety of sizes
- Made of tough, lightweight ABS plastic
- Flammability rating: UL94V-0
- Suggested service temperature -20C to +70C
- Optional close-fitting covers are available for all sizes
- Finish: Black
- Shipped in packages of 10 pieces per catalog number

Potting Boxes - Style A											
Catalog Number	Drawings	Weight (Ozs.)	A	B	C	D	E	F	G	Covers	Drawings
PB-1558	PDF DXF	5	2.00"	1.50"	1.00"	1.86"	1.36"	.93"	.84"	PBC-1558-CN	PDF DXF
PB-1559	PDF DXF	10.5	3.00"	2.00"	1.50"	2.86"	1.86"	1.43"	1.34"	PBC-1575-C	PDF DXF
PB-1560 **	PDF DXF	1.2	.79"	.79"	.51"	.73"	.73"	.48"	.45"	PBC-1560-C	PDF DXF
PB-1561 **	PDF DXF	3.3	1.97"	.52"	.59"	1.87"	.42"	.54"	.50"	PBC-1561-C	PDF DXF
PB-1562 **	PDF DXF	3.2	.97"	.97"	.97"	.89"	.89"	.93"	.89"	PBC-1562-C	PDF DXF
PB-1563 **	PDF DXF	5.1	1.57"	1.57"	.78"	1.49"	1.49"	.74"	.70"	PBC-1563-C	PDF DXF
PB-1564 **	PDF DXF	5.0	1.80"	1.20"	.63"	1.70"	1.10"	.58"	.56"	PBC-1564-C	PDF DXF
PB-1565 **	PDF DXF	15.7	2.72"	1.90"	1.37"	2.62"	1.80"	1.32"	1.25"	PBC-1565-C	PDF DXF
PB-1575	PDF DXF	9.5	3.00"	2.00"	.90"	2.86"	1.86"	.83"	.76"	PBC-1575-C	PDF DXF
PB-1576	PDF DXF	13	3.00"	3.00"	1.50"	2.86"	2.86"	1.41"	1.36"	PBC-1576-C	PDF DXF
PB-1577	PDF DXF	2.5	1.00"	1.00"	.75"	.88"	.88"	.69"	.61"	PBC-1577-C	PDF DXF
PB-1578	PDF DXF	15	4.00"	2.12"	2.00"	3.86"	1.98"	1.93"	1.86"	PBC-1578-C	PDF DXF
PB-1579	PDF DXF	3	1.50"	1.25"	.80"	1.36"	1.11"	.73"	.66"	PBC-1579-C	PDF DXF
PB-1580	PDF DXF	11	4.00"	1.75"	1.00"	3.86"	1.61"	.93"	.86"	PBC-1580-C	PDF DXF
PB-1581	PDF DXF	3	2.09"	1.25"	.44"	1.95"	1.11"	.37"	.30"	PBC-1581-C	PDF DXF
PB-1582	PDF DXF	12	4.00"	2.12"	.90"	3.86"	1.98"	.83"	.76"	PBC-1578-C	PDF DXF
PB-1583	PDF DXF	28	4.37"	3.12"	2.00"	4.17"	2.92"	1.90"	1.79"	PBC-1583-C	PDF DXF

** Sold in quantities of 25, UL94-HB flammability rating