




INDUSTRIAL BUZZERS

ACOUSTIC



Acoustic Signals Industrial Buzzers > Adaptahorn Series

Product overview

The Adaptahorn buzzer has a powerful output giving a penetrating, low frequency sound. With a variety of

mounting options, they can be used in almost any application, both indoors and outdoors. Adaptahorns are available as a grill version for flush mounting and also as a weatherproof version.

Features

High output
penetrating sound
Durable, long life
mechanism
Continuously rated

Material
Zinc Alloy

Code No:	Voltage:	Frequency:	Current:
ABK875-G1	24v Dc ---	350-400 Hz	0.16 A
ABK874-N5	120v Ac ~	350-400 Hz	0.13 A
ABK874-R5	230v Ac ~	350-400 Hz	0.06 A
Weatherproof Type			
ABK877-G1	24v Dc ---	350-400 Hz	0.16 A*
ABK876-N5	120v Ac ~	350-400 Hz	0.13 A*
ABK876-R5	230v Ac ~	350-400 Hz	0.06 A*



Kg 1.2/1.6*

50/60 Hz

°C -35+66

IP 44/65*

CONTINUOUS

INDUSTRIAL

APPROVAL AND CONFORMITIES



CE

IP 44/65*

CONTINUOUS


INDUSTRIAL

dB 112



ELECTRONIC

ACOUSTIC



Acoustic Signals Electronic Sounders > AE40M Series

Product overview

The AE40M Series is an 8-tone electronic sounder available in 10-30v Dc and 230v Ac versions. This product is ideal for fire alarm and close proximity

industrial applications. The Dc version is available in both deep base or shallow base, with deep base offering side entry and increased IP protection. The Ac version is deep base as standard.

Features

Low current consumption

IP54 or 65

Selectable tones (8)

Suitable for use with the Easy AVR upgrade LED

Material
ABS Plastic

Code No:	Voltage:	Frequency:	Current:
AE40M-24R-SB	10-30v Dc ---	800-2580 Hz	32 mA*
AE40M-24R*	10-30v Dc ---	800-2580 Hz	32 mA*
AE40M-230R*	230v Ac ~	800-2580 Hz	50 mA

* Current at 24v Dc ---



Kg 0.32

°C -20+45

IP 54/65*

8 TONES CONTINUOUS

FIRE

dB 100

APPROVAL AND CONFORMITIES



CE

IP 54/65*

8 TONES CONTINUOUS

FIRE

dB 100

INDUSTRIAL