

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [55451-2870](#)
Status: **Active**
Description: 1.25mm Pitch Mi II™ System Wire-to-Board Header, Dual Row, Vertical, Lead-Free, 28 Circuits

Documents:
[3D Model](#) [Product Specification PS-54596-019 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family PCB Headers
Series [55451](#)
Application Signal, Wire-to-Board
Product Name Mini Mi II™
UPC 756054760888

Physical
Breakaway No
Circuits (Loaded) 28
Circuits (maximum) 28
Color - Resin Natural
Durability (mating cycles max) 30
First Mate / Last Break No
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 1165.000/mg
Number of Rows 2
Orientation Vertical
PC Tail Length 3.00mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 1.25mm
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Through Hole

Electrical
Current - Maximum per Contact 1.5A
Voltage - Maximum 100V

Material Info

Reference - Drawing Numbers
Product Specification PS-54596-019
Sales Drawing SD-55451-006



EU RoHS
ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS

Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[55451Series](#)

Mates With
[54596](#) IDT Receptacle Housing

This document was generated on 11/11/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION