



High Energy type Capacitors Series DZ

- Low internal resistance allows boosting charge and heavy-current discharge. (ampere level)
- Pollution-Free ; with no pollutants such as Cd or Pb.
- Unlimited number of charges and discharges.




Marking color : White print on a black sleeve

Specifications

Item	Performance									
Category temperature range (°C)	-25 to +70									
Tolerance at rated capacitance (%)	-20 to +80									
Internal resistance at 1 kHz	Rated Capacitance (F)		1.0	3.3	4.7	10	20	50	100	200
	Internal resistance (Ω)		1.0	0.3	0.2	0.2	0.2	0.08	0.08	0.08
Characteristics at high and low temperature	Percentage of capacitance change		Within ±30% of value at 20°C							
	Internal resistance		Less than five times of the value at 20°C							
Endurance (70°C)	Test time		1000 hours							
	Percentage of capacitance change		Within ±30% of the initial measured value							
	Internal resistance		Within four times of the initial specified value							
Shelf life (70°C)	Test time :1000 hours ; Same as endurance.									

Outline Drawing

Unit: mm



Standard Ratings

Max. operating voltage(V)	Rated capacitance(F)	Max. Leakage Current(mA) after 24h	ELNA Parts No.	φ DxL(mm)	Internal resistance(mΩ) at 1kHz (measurement value)
2.5	1.0	0.1	DZ-2R5D105	8.0x22.0	200
2.5	3.3	0.2	DZ-2R5D335	12.5x23.0	70
2.5	4.7	0.3	DZ-2R5D475	12.5x31.5	50
2.5	10	0.5	DZ-2R5D106	18.0x35.0	30
2.5	20	0.8	DZ-2R5D206	18.0x40.0	30
2.5	50	1.0	DZ-2R5D506	25.0x40.0	20
2.5	100	1.0	DZ-2R5D107	35.0x50.0	20
2.5	200	2.0	DZ-2R5D207S57	35.0x50.0	20

* Internal resistance are not guaranteed values, but measurement value.

* We tailor packaged product in series and parallel arrangements according to voltage and capacitance as required.

Part numbering system (example: 2.5V10F)

Environmental item	DZ	—	2R5	D	106	T
	Series code		Rated voltage symbol		Rated capacitance symbol	
Former item	DZ	—	2R5	D	106	
	Series code		Rated voltage symbol		Rated capacitance symbol	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Elna:

[DZ-2R5D506N](#) [DZ-2R5D334](#) [DZ-2R5D107](#) [DZ-2R5D106](#) [DZ-2R5D335N](#) [DZ-2R5D107N](#) [DZ-2R5D506](#) [DZ-2R5D475](#) [DZ-2R5D335T](#) [DZ-2R5D105T](#) [DZ-2R5D106T](#) [DZ-2R5D475T](#)