

Marine Products 30 Ampere, 125 Volt Cable Set

Features and Benefits

UL Listed.

Available in 25', 35' and 50' lengths.

Jute fillers inside jacket for maximum cable flexibility. Hubbell cable coils neater, lighter, lays flatter.

Molded flexneck adds life to cable set by preventing right-angle cable damage and pullout.

Strain relief bull ring protects against stress and strain on the conductors caused by boat movement, crew traffic, rough handling.

Molded design totally encased in solid PVC material, for superior waterproofing and durability.

Exclusive copper crimp barrel termination provides protection against internal overheating and burnout compared to screw terminals or brass crimps. These copper crimps are the same type used by power companies. The result: tighter connections, better conductivity, longer life.

Locking ring assures proper alignment of connector to inlet for complete contact and waterproofing. Prevents accidental disengagement.

Arrow indicating lock position.

Line-up notches to indicate: Locked - Unlocked.

Arrow with ground symbol allows lining up with ground of receptacle.

New improved styling.

Arrow indicating unlock position.



Wiring Device-Kellems

www.hubbell-marine.com

Marine Products
30 Ampere, 125 Volt
2 Pole 3 Wire
Ship-to-Shore Devices



Our 30A, 125V cable set is packed with details end to end that make a high performance difference. Completely factory pre-wired with molded-on devices. Designed to coil easily and lie flat.



IP56
SUITABILITY
(Boatside)



HBL61CM08W



YC310250

30A 125V Shore Power Cable Set


Description	Catalog Numbers
50' yellow vinyl jacketed shore power cable set. #10 AWG is factory pre-wired with molded-on devices. Connector end has non-metallic threaded sealing ring which makes inlet/connector interface watertight.	HBL61CM08
Same as #HBL61CM08 except 35' in length.	HBL61CM05
Same as #HBL61CM08 except 25' in length.	HBL61CM03
50' white shore power cableset.	HBL61CM08W
25' white shore power cableset.	HBL61CM03W
Three conductor, #10 AWG type STW, yellow PVC jacketed portable cord with jute fillers for added flexibility. Ideal for making cable sets, extension cord, and adapters as it will not mark boat's deck. 250' lengths only.	YC310250
Three conductor, #10 AWG type STW, white PVC jacketed portable cord with jute fillers for added flexibility. Ideal for making cable sets, extension cord, and adapters as it will not mark boat's deck. 280' lengths only.	WC310280



Marine Products Stylized Line of Shore Power Inlets

Contemporary Styling — Hubbell Quality

30 Amp Interior




Fits most mounting patterns.

Contacts are nickel plated brass for corrosion resistance.

New easy-to-wire interior is transparent for quick, visual inspection of terminations.

Includes #SR3050 protective rear enclosure cap attaches to contact carrier with 3 screws.

50 Amp Interior



Thermoset contact carrier is arcing and heat resistant.

Notched contact carrier enables wiring of interior while in place.

Pressure screw terminals for secure terminations - clearly marked for easy identification.

Optional #SR3050 protective rear enclosure cap attaches to contact carrier with 3 screws.

Fits most mounting patterns.

Take advantage of these contemporary shore power inlets – in either rugged thermoplastic or corrosion resistant stainless steel – to add the finishing touch to a boat going into production or to modernize a boat that's seen many seasons of use. Both the gleaming, white Centrex® non-metallic models and the brushed, type 316 stainless steel models offer the same features. For starters, you'll be glad to hear that these Hubbell shore power inlets install as easy as 1-2-3 and match most mounting patterns available. Then you'll discover that they have a lot of built-in extras like a friction-tight cover that automatically holds the cover open while inserting the cable set. Plus, you'll find inside a genuine Hubbell wiring device with all of the quality characteristics that have made Hubbell the marine electrical products leader. What's more, you can complement these stylish devices with phone and TV inlets for a complete family.

Stylized Watertight Stainless Steel Shore Power Inlet Series

- #316 stainless steel for corrosion resistance.
- Does not require screwing down of cover for water resistance.
- Fully watertight when locked closed to comply with ABYC recommendations (E-8.21).

Stylized Weatherproof Non-Metallic Shore Power Inlet Series

- Centrex non-metallic cover is specifically designed for outdoor use with outstanding UV resistance, impact resistance and weatherability.
- Meets ABYC (E-8.21) recommendations for inlets installed in weatherproof areas.



Centrex® is a registered trademark of Monsanto; Rynite® is a trademark of E. I. DuPont.

Marine Products

30 Ampere, 125 Volt

2 Pole 3 Wire

Ship-to-Shore Devices



IP56
SUITABILITY Inlets Only.



30A 125V Ship-to-Shore Devices

Description	Catalog Numbers
Stylized UV resistant non-metallic shore power inlet has white Centrex cover which makes unit weatherproof when completely closed. Interior has easy-to-wire terminations and is transparent for quick and easy visual inspection. Mounting holes are 2 3/8" (60.3) on centers and match existing mounting patterns. Mounting screws and gasket included. Protective rear enclosure/strain relief also included.	HBL303NM
Stylized type 316 stainless steel shore power inlet has easy to use push-button latch that makes unit watertight when fully engaged. Interior has easy-to-wire terminations and is transparent for quick and easy visual inspection. Mounting holes are 2 3/8" (60.3) on centers and match existing mounting patterns. Mounting screws and gasket included. Protective rear enclosure/strain relief also included.	HBL303SSBL
Traditional, stainless steel shore power inlet has new easy-to-wire terminations. Interior is transparent for quick and easy visual inspection. Interior is shielded from the elements by a gasketed, self-closing cover, watertight when cover is screwed in place. Mounting holes are 2 3/8" (60.3) on centers. Mounting screws and gasket included. Protective rear enclosure/strain relief also included.	HBL303SS
Protective rear cover. Fits all 30 Amp shore power inlets. Secures to back of inlets with 3 screws which are provided.	SR3050
Replacement interior for #HBL303SS and #60CM61 shore power inlets.	HBL303INT
Nickel plated brass adapter plate for mounting chrome plated brass shore power inlets to FS/FD box.	HBL60CM75*
Stainless steel power outlet has gasketed, self-closing cover, watertight when cover is screwed in place. Mounting holes are 2 3/8" (60.3) on centers. Mounting screws and gasket included.	HBL303SSO

*Not shown.



HBL303NM




HBL303SSBL



HBL303SS

30A 125V Traditional Metallic Inlets



SR3050



HBL303SSO

Marine Products 30 Ampere, 125 Volt

2 Pole 3 Wire
Ship-to-Shore Devices



HBL26CM10



HBL26CM11



HBL60CM31



HBL26CM13



HBL60CM33



HBL60CM32



Plugs, receptacles and
connectors only.

IP20

SUITABILITY Plugs and connectors only.



30A 125V

30A 125V Ship-to-Shore Devices

Description	Catalog Numbers
Yellow single receptacle has Rynite® body and abuse resistant nylon face.	HBL26CM10
Yellow Insulgrip® plug has rugged nylon housing and cord grip with range of .325" to .930" (8-24) that utilizes a unique offset jaws arrangement to provide secure strain relief.	HBL26CM11
Yellow Seal-Tite® cover for weatherproofing #HBL26CM11 or #HBL23CM11 plugs. IP55 SUITABILITY. <i>Note: Fits Insulgrip® devices only.</i>	HBL60CM31
White vinyl Seal-Tite® cover for weatherproofing #HBL26CM11 or #HBL23CM11 plugs. IP55 SUITABILITY. <i>Note: Fits Insulgrip® devices only.</i>	HBL60CM31W*
Yellow Insulgrip® connector body has rugged nylon housing and cord grip with range of .325" to .930" (8-24) that utilizes a unique offset jaws arrangement to provide secure strain relief	HBL26CM13
Yellow Seal-Tite® cover for weatherproofing #HBL26CM13 or #HBL23CM13 connector bodies when used with shore power inlets. Threaded sealing ring makes connection watertight. Also for weatherproofing #HBL26CM11 plug when used with #HBL303SSO power outlet. IP56 SUITABILITY. <i>Note: Fits Insulgrip® devices only.</i>	HBL60CM33
White Seal-Tite® cover for weatherproofing #HBL26CM13 or #HBL23CM13 connector body when used with shore power inlets. Threaded sealing ring makes connection watertight. Also for weatherproofing #HBL26CM11 plug when used with #HBL303SSO power outlet. IP56 SUITABILITY. <i>Note: Fits Insulgrip® devices only.</i>	HBL60CM33W*
Yellow Seal-Tite® cover for weatherproofing #HBL26CM13 or #HBL23CM13 connector bodies when used on extension cords or adapters. IP55 SUITABILITY. <i>Note: Fits Insulgrip® devices only.</i>	HBL60CM32
Yellow polycarbonate spring-loaded lift cover plate for weatherproofing <i>old</i> style #26CM10 receptacle. Meets the most stringent requirements of UL's three listing categories for weatherproof plates. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP44 SUITABILITY.	HBL74CM24WO**
Same as #HBL74CM24WO except gray in color. IP44 SUITABILITY.	HBL7424WO**
Yellow polycarbonate spring-loaded lift cover plate for weatherproofing #HBL26CM10 receptacle. Meets the most stringent requirements of UL's three listing categories for weatherproof plates. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP44 SUITABILITY.	HBL74CM25WOA**
Same as #HBL74CM25WOA except gray in color. IP44 SUITABILITY.	HBL7425WOA**
Stainless steel wallplate for <i>old</i> #23CM10 or #26CM10.	S725*
Stainless steel wallplate for new #HBL23CM10 or #HBL26CM10.	S720*

*Not shown.

**See page V-47 for photo.

Rynite® is a registered trademark of E. I. DuPont.



Wiring Device-Kellems www.hubbell-marine.com

Marine Products

30 Ampere, 125 Volt

2 Pole 3 Wire

Ship-to-Shore Devices



Plugs and connectors only.

IP20

SUITABILITY Plugs and connectors only.



30A 125V Ship-to-Shore Devices

Description	Catalog Numbers
Yellow Valise® plug has one-piece nylon housing and assembles easily with two screws. Built-in cord grip has range of .590"-.930" (15.0-23.6).	HBL26CM11V
Black Valise® plug for use on bass boats with trolling motor. One-piece nylon housing assembles easily with two screws. Built-in cord grip has a range of .590"-.930" (15.0-23.6).	HBL26CM11VB
Yellow vinyl Seal-Tite® cover for weatherproofing #HBL23CM11V or #HBL26CM11V plugs. IP55 SUITABILITY. <i>Note: Fits Valise® devices only.</i>	HBL60CM31V
Yellow Valise® connector body has a one-piece nylon housing and assembles easily with two screws. Built-in cord grip has range of .590"-.930" (15.0-23.6).	HBL26CM13V
Yellow vinyl Seal-Tite® cover for #HBL26CM13V connector body when used with shore power inlets. Threaded sealing ring makes connection watertight. IP56 SUITABILITY. <i>Note: Fits Valise® devices only.</i>	HBL60CM33V
Yellow vinyl Seal-Tite® cover for weatherproofing #HBL23CM13V or #HBL26CM13V connector bodies when used on extension cords or adapters. IP55 SUITABILITY. <i>Fits Valise® devices only.</i>	HBL60CM32V
Replacement non-metallic sealing ring for 30A cable sets and boots.	RPL30P



HBL26CM11V



HBL26CM11VB



HBL60CM31V



RPL30P



HBL26CM13V



HBL60CM33V



HBL60CM32V

Valise Plug

