

5.7" Open Frame

Part No	:	HE057AV
Item Description	:	5.7" monitor / without touch/RGB/video

Advantage and Application ■ long term availability of adopted TFT LCD panels (stability of supply for min. 3 years) ■ Analog RGB / Video supportable ■ Touch screen (not adopted) ■ RS232 communication (option) ■ Fine finishing metal chassis (brilliant design & complete set level OSD button) ■ Application - Kiosks - ATMs - Casino & Amusement games - Lottery and Ticket sales - Self-Services - Industrial process control	Item	Description
	Frame / bezel Color	EGL in black
	Display Type	Size: 5.7" diagonal, Type: Active matrix TFT LCD Aspect ratio: 4 x 3
	Active area	115.2 (H) x 86.4 (V)
	Optimal (native) resolution	640 x 480
	Support color	262K colors
	Brightness (without touch)	700 cd/m2
	Viewing Angles	80 / 80 / 70 / 70
	Input video supportable	Analog RGB, C-VBS, S-VHS
	Temperature	Operating ; - 30°C ~ +85 °C Storage : - 30°C ~ +85 °C
	Mounting Holes	VESA / 75 x 75 mm
	Applicable Graphic Mode	VESA standard timing control
	Weight & Volume	Unit Weight : 830 g, Carton Packing : pcs Carton weight : Kg

