

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300940314

Status:

Active

Overview:

Support Grips

Description:

Standard Duty Support Grip, Single Eye, Split Lace, Single Weave, Cable Diameter 19.05-25.15mm (.750-.990"), Approximate Break Strength 598.74kg (1320 lbs)

Documents:

Brochure (PDF)RoHS Certificate of Compliance (PDF)

Agency Certification

CSALR32159

General

Product FamilyCable Grips

Series130094

Eye TypeSingle

O-RingN/A

OverviewSupport Grips

Product NameStandard Duty

TypeSupport Grip

UPC78678835167

Physical

Approximate Break Strength598.74kg (1320 lbs)

Bale Length0.203m (8.00")

Body StyleStraight

Cable Diameter19.05-25.15mm (.750-.990")

Color - GrommetN/A

GenderN/A

Material - BodyN/A

Material - GripNon-magnetic Tin Bronze Wire


Mesh Length0.356m (14.00")

Number of HolesN/A

Thread SizeN/A

Material Info

Engineering Number35167



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

130094 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION