



WALL MOUNT ENCLOSURES

SECTION

02

100 SERIES
w/Fixed Side Panels

200 SERIES
w/Removable Side Panels

300 SERIES
w/Swing Out Design

600 – EZ-ASSEMBLY SERIES
w/Fixed Side Panels



WALL MOUNT ENCLOSURES

100 Fixed Side Panel Series **Page No.**

100 Series **25-26**

200 Removable Side Panel Series **Page No.**

200 Series **NEW SIZES** **27-28**

300 Swing-Out Design Series **Page No.**

300 Series **NEW SIZES** **29-30**

600 EZ-Assembly Series **Page No.**

600 Series **31-32**

DVR DVR Security Enclosures **Page No.**

DVR Series **NEW SIZES** **33-34**

SECTION

02



WALL MOUNT ENCLOSURES

100 SERIES FIXED SIDE PANELS

SECTION

02



100 Fixed Side Panel Series

100 Series

External Rack Size Height	11.5" (5U) 15" (7U) 18" (9U) 22" (11U)
External Rack Size Width	20.5"
External Rack Size Depth	20"
Mounting Format (Internal)	19"
Reversible Front Locking Door	Smoked Acrylic
Vented Side Panels	Fixed
Hinged Swing Out Design	No
Reinforced Door Frame	Yes
Front Cage Rails	Yes
Single Key Lock Set	2 keys per set
Cable Access	Top: Cutouts Bottom: Cutouts
Electrostatic Powdercoat MicroFinish	Black & Ivory
Preinstalled 80CFM 110V Fans	1
Cage Nuts, Screws & Washers	12 Each
Compliance	EIA-310D
Delivery Style	Assembled

100 Structure and Fabrication

Item No.	Color	Rack Units (U)	Structure (AWG)	Side Panels (AWG)	Top Panel (AWG)	Base (AWG)
WM1019-05-01	Ivory	5U	18	18	18	18
WM1019-05-02	Black	5U	18	18	18	18
WM1019-07-01	Ivory	7U	18	18	18	18
WM1019-07-02	Black	7U	18	18	18	18
WM1019-09-01	Ivory	9U	18	18	18	18
WM1019-09-02	Black	9U	18	18	18	18
WM1019-11-01	Ivory	11U	18	18	18	18
WM1019-11-02	Black	11U	18	18	18	18

WALL MOUNT ENCLOSURES

100 SERIES FIXED SIDE PANELS



100 Fixed Side Panel Series

Item No.	Rack Units (1U=1.75") 19" Format	External Dimensions (inch)			Internal Dimensions (inch)			Load Capacity (lbs.)	Shipping Weight (Assembled)	Shipping Weight (Knockdown)
		H	W	D	H	W	D¹			
WM1019-05-01 WM1019-05-02	5U	11.5"	20.5"	20"	9"	19"	18"	130	36	N/A
WM1019-07-01 WM1019-07-02	7U	15"	20.5"	20"	12.5"	19"	18"	130	41	N/A
WM1019-09-01 WM1019-09-02	9U	18"	20.5"	20"	16"	19"	18"	130	46	N/A
WM1019-11-01 WM1019-11-02	11U	22"	20.5"	20"	19.5"	19"	18"	130	51	N/A

1- Internal dimensions measure from front rails to back door. All Wall Mount Enclosures have an additional 2" usable space from rails to front door.

SECTION

02

100 Reversible Locking Front Door



Front locking door is reversible for left or right side opening.

100 Vented Fixed Side Panels



Vented fixed side panels for better air flow and equipment cooling.

100 Adjustable Cage Nut Rails



Includes adjustable cage nut rails and cage nuts with standard #12-24 mounting screws. All cage nut rails are marked with an RU space index for easy alignment when mounting equipment.

100 Pre-Installed Cooling Fan



Pre-Installed 110VAC 80CFM fan units keep equipment running cool.

100 Ships Fully Assembled



All sizes are UPS shippable and ready for out -of-the-box installation.





WALL MOUNT ENCLOSURES

200 SERIES

REMOVABLE SIDE PANELS

NEW SIZES

200 Removable Side Panel Series

200 Series	Standard Depth	Extended Depth
External Rack Size Height	12.5" (5U) 16" (7U) 19.5" (9U) 23" (11U) 28" (14U) 31.5" (16U)	36" (20U) 48" (28U)
External Rack Size Width	21"	21"
External Rack Size Depth	20"	28"
Mounting Format (Internal)	19"	19"
Reversible Front Locking Door	Smoked Acrylic	Smoked Acrylic
Vented Side Panels	Removable	Removable
Hinged Swing Out Design	No	No
Reinforced Door Frame	Yes	Yes
Front Cage Rails	Yes	Yes
Single Key Lock Set	2 keys per set	2 keys per set
Cable Access	Top:Cutouts Bottom:Cutouts	Top:Cutouts Bottom:Cutouts
Electrostatic Powdercoat MicroFinish	Black & Ivory	Black & Ivory
Preinstalled 80CFM 110V Fans	1	1
Cage Nuts, Screws & Washers	12 Each	12 Each
Compliance	EIA-310D	EIA-310D
Delivery Style	Assembled	Assembled

SECTION

02



200 Structure and Fabrication

Item No.	Color	Rack Units (U)	Structure (AWG)	Side Panels (AWG)	Top Panel (AWG)	Base (AWG)
WM2019-05-01	Ivory	5U	18	18	18	18
WM2019-05-02	Black	5U	18	18	18	18
WM2019-07-01	Ivory	7U	18	18	18	18
WM2019-07-02	Black	7U	18	18	18	18
WM2019-09-01	Ivory	9U	18	18	18	18
WM2019-09-02	Black	9U	18	18	18	18
WM2019-11-01	Ivory	11U	18	18	18	18
WM2019-11-02	Black	11U	18	18	18	18
WM2019-14-01	Ivory	14U	18	18	18	18
WM2019-14-02	Black	14U	18	18	18	18
WM2019-16-01	Ivory	16U	18	18	18	18
WM2019-16-02	Black	16U	18	18	18	18
WM 2019-20-02	Black	20U	18	18	18	18
WM 2019-28-02	Black	28U	18	18	18	18

WALL MOUNT ENCLOSURES

200 SERIES

REMOVABLE SIDE PANELS



200 Removable Side Panel Series

Item No.	Rack Units (1U=1.75") 19" Format	External Dimensions (inch)			Internal Dimensions (inch)			Load Capacity (lbs.)	Shipping Weight (Assembled)	Shipping Weight (Knockdown)
		H	W	D	H	W	D'			
WM2019-05-01 WM2019-05-02	5U	12.5"	21"	20"	9"	19"	16"	130	39	N/A
WM2019-07-01 WM2019-07-02	7U	16"	21"	20"	12.5"	19"	16"	130	43	N/A
WM2019-09-01 WM2019-09-02	9U	19.5"	21"	20"	16"	19"	16"	130	47	N/A
WM2019-11-01 WM2019-11-02	11U	23"	21"	20"	19.5"	19"	16"	130	52	N/A
WM2019-14-01 WM2019-14-02	14U	28"	21"	20"	24.5"	19"	16"	130	57	N/A
WM2019-16-01 WM2019-16-02	16U	31.5"	21"	20"	28"	19"	16"	130	61	N/A
WM2019-20-02	20U	38.5"	21"	28"	35"	19"	24"	130	70	N/A
WM2019-28-02	28U	52.5"	21"	28"	49"	19"	24"	130	86	N/A

SECTION

02

NEW

1 - Internal dimensions measure from front rails to back door. All Wall Mount Enclosures have an additional 2" usable space from rails to front door.

200 Reversible Locking Front Door



Front locking door is reversible for left or right side opening.



200 Vented Removable Side Panels



Vented removable side panels with key lock for secure and easy access.

200 Adjustable Cage Nut Rails



Includes adjustable cage nut rails and cage nuts with standard #12-24 mounting screws. All cage nut rails are marked with an RU space index for easy alignment when mounting equipment.

200 Pre-Installed Cooling Fans



Pre-Installed 110VAC 80CFM fan units keep equipment running cool.

200 Ships Fully Assembled



All 5U to 11U sizes are UPS shippable and ready for out-of-the-box installation.



WALL MOUNT ENCLOSURES

300 SERIES

SWING-OUT W/FIXED SIDE PANELS

NEW SIZES

300 Swing-Out Design Series

300 Series	Standard Depth	Extended Depth
External Rack Size Height	15" (7U) 18.5" (9U) 22" (11U) 27" (14U) 30.5" (16U)	37.5" (20U) 51.5" (28U)
External Rack Size Width	20.5"	20.5"
External Rack Size Depth	23.5"	30.5"
Mounting Format (Internal)	19"	19"
Reversible Front Locking Door	Smoked Acrylic	Smoked Acrylic
Vented Side Panels	Fixed	Fixed
Hinged Swing Out Design	Yes	Yes
Reinforced Door Frame	Yes	Yes
Front Cage Rails	Yes	Yes
Single Key Lock Set	2 keys per set	2 keys per set
Cable Access	Top:Cutouts Bottom:Cutouts	Top:Cutouts Bottom:Cutouts
Electrostatic Powdercoat MicroFinish	Black & Ivory	Black & Ivory
Preinstalled 80CFM 110V Fans	1	1
Cage Nuts, Screws & Washers	12 Each	12 Each
Compliance	EIA-310D	EIA-310D
Delivery Style	Assembled	Assembled

SECTION

02



300 Structure and Fabrication

Item No.	Color	Rack Units (U)	Structure (AWG)	Side Panels (AWG)	Top Panel (AWG)	Base (AWG)
WM3019-05-01	Ivory	5U	18	18	18	18
WM3019-05-02	Black	5U	18	18	18	18
WM3019-07-01	Ivory	7U	18	18	18	18
WM3019-07-02	Black	7U	18	18	18	18
WM3019-09-01	Ivory	9U	18	18	18	18
WM3019-09-02	Black	9U	18	18	18	18
WM3019-11-01	Ivory	11U	18	18	18	18
WM3019-11-02	Black	11U	18	18	18	18
WM3019-14-01	Ivory	14U	18	18	18	18
WM3019-14-02	Black	14U	18	18	18	18
WM3019-16-01	Ivory	16U	18	18	18	18
WM3019-16-02	Black	16U	18	18	18	18
WM 3019-20-02	Black	20U	18	18	18	18
WM 3019-28-02	Black	28U	18	18	18	18

WALL MOUNT ENCLOSURES

300 SERIES

SWING-OUT W/FIXED SIDE PANELS



300 Swing-Out Design Series

Item No.	Rack Units (1U=1.75") 19" Format	External Dimensions (inch)			Internal Dimensions (inch)			Load Capacity (lbs.)	Shipping Weight (Assembled)	Shipping Weight (Knockdown)
		H	W	D	H	W	D'			
WM3019-07-01 WM3019-07-02	7U	15	20.5"	23.5"	12.5"	19"	17"	130	46	N/A
WM3019-09-01 WM3019-09-02	9U	18.5	20.5"	23.5"	16"	19"	17"	130	51	N/A
WM3019-11-01 WM3019-11-02	11U	22"	20.5"	23.5"	19.5"	19"	17"	130	56	N/A
WM3019-14-01 WM3019-14-02	14U	27"	20.5"	23.5"	24.5"	19"	17"	130	59	N/A
WM3019-16-01 WM3019-16-02	16U	30.5"	20.5"	23.5"	28"	19"	17"	130	67	N/A
WM3019-20-02	20U	37.5"	20.5"	30.5"	35"	19"	24"	130	83	N/A
WM3019-28-02	28U	51.5"	20.5"	30.5"	49"	19"	24"	130	115	N/A

1- Internal dimensions measure from front rails to back door. All Wall Mount Enclosures have an additional 2" of usable space from rails to front door and all 300 Series Wall Mount Enclosures have an additional 3" of usable space in the hinged rear door.

SECTION

02

NEW

300 Reversible Locking Front Door



Front locking door is reversible for left or right side opening.

300 Vented Fixed Side Panels



Vented fixed side panels for better air flow and equipment cooling.



300 Adjustable Cage Nut Rails



Includes adjustable cage nut rails and cage nuts with standard #12-24 mounting screws. All cage nut rails are marked with an RU space index for easy alignment when mounting equipment.

300 Swing-Out Locking Design



Swing-Out feature allows easy access to back of equipment with key lock to prevent tampering.

300 Pre-Installed Cooling Fans



Pre-Installed 110VAC 80CFM fan units keep equipment running cool.

300 Ships Fully Assembled



All 5U to 11U sizes are UPS shippable and ready for out-of-the-box installation.



WALL MOUNT ENCLOSURES

600 SERIES

EZ-ASSEMBLY W/FIXED SIDE PANELS

600 EZ-Assembly Series

600 Series

External Rack Size Height	15" (7U) 18" (9U) 22" (11U)
External Rack Size Width	20.5"
External Rack Size Depth	20"
Mounting Format (Internal)	19"
Reversible Front Locking Door	Smoked Acrylic
Vented Side Panels	Fixed
Hinged Swing Out Design	No
Reinforced Door Frame	Yes
Front Cage Rails	Yes
Single Key Lock Set	2 keys per set
Cable Access	Top: Cutouts Bottom: Cutouts
Electrostatic Powdercoat MicroFinish	Black
Preinstalled 80CFM 110V Fans	1
Cage Nuts, Screws & Washers	12 Each
Compliance	EIA-310D
Delivery Style	Knockdown

SECTION

02

10-Minute
Assembly



600 Structure and Fabrication

Item No.	Color	Rack Units (U)	Structure (AWG)	Side Panels (AWG)	Top Panel (AWG)	Base (AWG)
EZ19-07-02	Black	7U	18	18	18	18
EZ19-09-02	Black	9U	18	18	18	18
EZ19-11-02	Black	11U	18	18	18	18

EZ-Assembly Instructions




Install top and bottom panels by tightening the nuts on the rear panel.



Pre-position for desired equipment depth and install left and right rails.



Install the left and right panels with the supplied mounting screws.



Install the front door by aligning with the corresponding side panel; right or left hand opening.

WALL MOUNT ENCLOSURES

600 SERIES

EZ-ASSEMBLY W/FIXED SIDE PANELS



600 EZ-Assembly Series

Item No.	Rack Units (1U=1.75") 19" Format	External Dimensions (inch)			Internal Dimensions (inch)			Load Capacity (lbs.)	Shipping Weight (Assembled)	Shipping Weight (Knockdown)
		H	W	D	H	W	D¹			
EZ19-07-02	7U	15"	20.5"	20"	12.5"	19"	18"	130	Use WM1019-07-xx	37
EZ19-09-02	9U	18"	20.5"	20"	16"	19"	18"	130	Use WM1019-09-xx	40
EZ19-11-02	11U	22"	20.5"	20"	19.5"	19"	18"	130	Use WM1019-11-xx	47

1 - Internal dimensions measure from front rails to back door. All Wall Mount Enclosures have an additional 2" usable space from rails to front door.

SECTION

02

600 Reversible Locking Front Door



Front locking door is reversible for left or right side opening.

600 Vented Fixed Side Panels



Vented fixed side panels for better air flow and equipment cooling.

600 Adjustable Cage Nut Rails



Includes adjustable cage nut rails and cage nuts with standard #12-24 mounting screws. All cage nut rails are marked with an RU space index for easy alignment when mounting equipment.

600 Pre-Installed Cooling Fan



Pre-Installed 110VAC 80CFM fan units keep equipment running cool.

600 Ships in Knockdown Box



All sizes are UPS shippable and are able to be assembled in less than 10 minutes.





DVR SECURITY ENCLOSURES

DVR SERIES SECURITY ENCLOSURES

DVR Security Enclosure Series

DVR Series

External Rack Size Height	9" 1(U)
External Rack Size Width	20"
External Rack Size Depth	21"
Mounting Format (Internal)	19"
Hinged Front Locking Door	Solid Metal or Clear Acrylic
Reinforced Door Frame	Yes
Rear Cage Mounts	Yes
Single Key Lock Set	2 keys per set
Cable Access	Rear: Cutouts
Electrostatic Powdercoat MicroFinish	Black
Preinstalled 80CFM 110V Fans	1
Cage Nuts, Screws & Washers	2 each
Compliance	EIA-310D
Delivery Style	Assembled

SECTION

02

NEW

Acrylic See-Thru Door



Solid Steel Door

DVR Structure and Fabrication

Item No.	Color	Door Structure	Rack Units (U)	Structure (AWG)	Side Panels (AWG)	Top Panel (AWG)	Base (AWG)
SE0920-21-02	Black	Solid Metal	1U	18	18	18	18
SE0920-21-02A	Black	Metal Frame with Acrylic Window	1U	18	18	18	18

DVR SECURITY ENCLOSURES

DVR SERIES SECURITY ENCLOSURES



DVR Security Enclosure Series

Item No.	Rack Units (1U=1.75") 19" Format	External Dimensions (inch)			Internal Dimensions (inch)			Load Capacity (lbs.)	Shipping Weight (Assembled)	Shipping Weight (Knockdown)
		H	W	D	H	W	D ¹			
SE0920-21-02 SE0920-21-02A	1U	9"	20"	21"	8"	19"	20"	130	27	N/A

1- Internal dimensions measure from front door to rear.

SECTION

02

DVR Removable Top Panel



Top panel is removable for easy access to equipment and wiring.

DVR Hinged Locking Front Door



Hinged front door is available in see-through acrylic or solid metal with key lock for secure and easy access.

DVR Fixed Cage Nut Mount



1U fixed cage nut mount for cage nuts threaded for standard #12-24 mounting screws.

DVR Pre-Installed Cooling Fan



Pre-Installed 110VAC 80CFM fan unit keeps equipment running cool.



Optional Accessories

DVR Wall Mount Brackets (#WB-SE-02)

Optional wall mount brackets allow flexibility of tabletop or wall mount installations.



DVR 12 Outlet AC Power Strip (#HPS-E12P)

Optional 1U 120VAC/12A EMI/RFI surge strip for powering DVR or other AC devices.

