




D




C



B



A



2129033-1: AS SHOWN

- 1 MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94 V-0, COLOR: BLACK.
CONTACT: COPPER ALLOY.
SHELL: STAINLESS STEEL.
- 2 FINISH:
CONTACT: Ni UNDER PL Au PL.
SHELL: Ni PL OVERALL.
- 3 SOLDER RING GAP SHOULD BE MIN. 0.2mm.

REFERENCE PIN DEFINITION

17	MICRO USB PIN 5	GND
16	MICRO USB PIN 4	ID
15	12P PIN 12	POWER GUN RETURN
14	12P PIN 11	POWER GUN RETURN
13	12P PIN 10	SIGNAL
12	12P PIN 9	SIGNAL
11	12P PIN 8	SIGNAL
10	12P PIN 7	SIGNAL
9	12P PIN 6	SIGNAL
8	12P PIN 5	SIGNAL
7	12P PIN 4	SIGNAL
6	12P PIN 3	SIGNAL
5	12P PIN 2	POWER
4	12P PIN 1	POWER
3	MICRO USB PIN 3	D+
2	MICRO USB PIN 2	D-
1	MICRO USB PIN 1	VBUS
PIN	CONTACT NO.	SIGNAL NAME

D

C

B

A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-



COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

-




SEE SHEET 1

-

-

-

4. PACKING MATERIAL:
TRAY: PS, THICKNESS=0.8±0.05mm,
COLOR: NATURAL.
5. NET WEIGHT: 1.856Kg,
GROSS WEIGHT: 3.586Kg.




100	16	2	3200
PCS/TARY	TRAY/INNER BOX	INNER BOX/CARTON	TOTAL Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

8 PLC ±
1 PLC ±
2 PLC ± ±1
3 PLC ± ±3°
4 PLC ±
ANGLES ±
FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

MICRO HYBIRD I/O 5+12
THROUGH HOLE,
PLUG ASSY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2129033

SCALE

SHEET

2 OF 2

REV

G1