


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT<br>PART # |          | STUD<br>SIZE | DIMENSIONS mm  |                |               |                |               |
|-------------------|----------|--------------|----------------|----------------|---------------|----------------|---------------|
|                   |          |              | A ±0,51        | W ±0,25        | C ±0,38       | M ±0,51        | H ±0,25       |
| PREF I X          | PK       |              |                |                |               |                |               |
| PM2-3F            | -C<br>-M | M3           | 16,00<br>(.63) | 5,84<br>(.23)  | 5,59<br>(.22) | 12,45<br>(.49) | 3,30<br>(.13) |
| PM2-4F            | -C<br>-M | M4           | 17,53<br>(.69) | 7,87<br>(.31)  | 6,35<br>(.25) | 13,46<br>(.53) | 4,57<br>(.18) |
| PM2-5F            | -C<br>-M | M5           | 18,03<br>(.71) | 8,64<br>(.34)  | 6,86<br>(.27) | 13,97<br>(.55) | 5,33<br>(.21) |
| PM2-6F            | -C<br>-M | M6           | 22,35<br>(.88) | 11,18<br>(.44) | 8,89<br>(.35) | 16,00<br>(.63) | 6,60<br>(.26) |

**NOTES:**

1. USED FOR:  
A. 1.5-2.5mm<sup>2</sup> (#16-14 AWG), SOLID  
OR STRANDED, COPPER WIRE
2. MATERIAL:  
A. STAMPING - 0.81mm (.03) THK COPPER, TIN PLATED
3. DIMENSIONS IN BRACKETS ARE IN INCHES
4. PACKAGE QTY:  
A. STD: C=100  
B. BULK: M=1000
5. WIRE STRIP LENGTH:  $7.1^{+.8}_{-0}$  ( $9/32^{+1/32}_{-0}$ )
6. INSTALLATION TOOLS: REF. DWGS.  
A41522, A41523, A41524, A41525



A41428\_01

|     |       |    |     |                                  |       |      |    |  <b>PANDUIT</b> CORP.      TINLEY PARK, ILLINOIS |       |               |                       |
|-----|-------|----|-----|----------------------------------|-------|------|----|---------------------------------------------------------------------------------------------------------------------------------------|-------|---------------|-----------------------|
| 01  | 10/97 | TM |     | CHANGED DECIMAL POINTS TO COMMAS |       |      |    | NON-INSULATED METRIC FORKS<br>1,5-2,5mm <sup>2</sup> BARREL                                                                           |       |               |                       |
| 00  | 11/91 | BK | RS  | RELEASED                         | 00687 | LA   | KS |                                                                                                                                       |       |               |                       |
| REV | DATE  | BY | CHK | DESCRIPTION                      | ECN # | CUST | PM | DRAWN BY<br>BDK                                                                                                                       | CHK'D | SCALE<br>NONE | DRAWING NO.<br>A41428 |