






© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS						DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION			
	✓		E	ECO-10-002921		PY 3-10	DM



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.010 ANGLES ±		CONTRACT NO 5-31-79		PART NO	
		DR <i>AM SHAPE</i>			
MATERIAL 23	CHK <i>1/5/79</i>		NAME PIN ASS'Y, RIGHT ANGLE 751 SERIES BOX CONNECTOR		
	APPD <i>1/5/79</i>		SIZE CODE IDENT NO DRAWING NO C 00779 531124		
FINISH 3	DSGN APPD		REV E		
	OTHER APPD		SCALE 4-1 SHEET 1 OF 2		

		REVISIONS				
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
				SEE SH 1		



5 KEY POSITION IDENTIFICATION MOLDED ON SURFACE SHOWN.

	6.675	89	7.340	7.630	180	1-531124-5
OBSOLETE	5.925	79	6.590	6.880	160	1- ↑ -4
	5.550	74	6.215	6.505	150	1- -3
OBSOLETE	4.425	59	5.090	5.380	120	1- -2
	4.050	54	4.715	5.005	110	1- -1
	3.675	49	4.340	4.630	100	1- -0
	OBSOLETE	3.300	44	3.965	4.255	90
OBSOLETE	2.925	39	3.590	3.880	80	-8
OBSOLETE	2.550	34	3.215	3.505	70	-7
	2.175	29	2.840	3.130	60	-6
	1.800	24	2.465	2.755	50	-5
	1.425	19	2.090	2.380	40	-4
	1.050	14	1.715	2.005	30	-3
OBSOLETE	.675	9	1.340	1.630	20	↓ -2
	.300	4	.965	1.255	10	531124-1
	D	C	B	A	NO. OF POS.	PART NO

		D	C	B	A	NO. OF POS.	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS $\pm .010$ ANGLES $\pm$	CONTRACT NO		AMP AMP INCORPORATED Harrisburg, Pa.				
	DR <i>AM SHAARPE</i> 6-4-79 CHK <i>[Signature]</i> 1/11						
MATERIAL	APPD <i>[Signature]</i> APPD <i>[Signature]</i>		NAME PIN ASS'Y, RIGHT ANGLE 751 SERIES BOX CONNECTOR				
	DSGN APPD OTHER APPD						
FINISH			SIZE	CODE IDENT NO	DRAWING NO	REV	
			C	00779	531124	E	
			SCALE 4-1		SHEET 2 OF 2		