



CABLE WHITE PRINT
USB CABLE E189529 AWG 2725 28AWG/1PR AND
24AWG/2C 80°C 30V VW-1

PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 5 Mohm(min)
4. dielectric test: DC 300V

⑧	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK "MADE IN CHINA" + "10PCS".
⑦	PE BAG	1	CLEAR SIZE: 130*280*0.05mm PRINT BLACK "MADE IN CHINA" + "1PC"
⑥	TIE	1	BLACK L=80mm
⑤	OUT JACKET	6g	BLACK PVC-40P (MOULD NO: WM-65)
④	OUT JACKET	6g	BLACK PVC-40P (MOULD NO: WM-40)
③	CABLE	1	BLACK USB1. 1 U12725 28# /1P+24# /2C+AEB OD: 4.7mm L=3000±10mm
②	CONN	1set	USB B MALE SHELL: NICKEL, PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
①	CONN	1set	USB A MALE SHELL: NICKEL, PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
NO.	NAME	SPECIFICATION	

CNC Tech, LLC			
Industrial Cable and Connector Technology			
DRAWN	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	101-1030-BL-00200
DECIDED		DATE	2012-02-15
VERSIONS/EDITION	A/0	PROJECTION	

