


### Adhesive Lined Grommet Edging

Grommet edging protects and prevents wires and cables from chafing against sharp edges of panel walls and knockouts. In addition to standard grommet edging, Panduit offers grommet edging with a pressure sensitive adhesive that lines the base of the product. This provides for an easy, clean, and secure application. Adhesive lined grommet edging is available in natural and weather resistant polyethylene and can be used on straight or irregular shaped surfaces. Adhesive lined grommet edging is a part of the innovative solutions Panduit provides to protect wire and cable to help you manage your physical infrastructure.

*To install, clean the edge of the panel, install the product over the edge of the panel, and then apply thumb pressure to activate the adhesive and the installation is complete.*



#### Key Features

#### Benefits

|                                           |                                                                                                                                      |
|-------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| <b>Polyethylene material</b>              | Economical, durable, and highly flexible; weather resistant option available                                                         |
| <b>Adhesive lined</b>                     | Ensures the product will stay where it is installed; eliminates messy, user supplied adhesives for a faster and cleaner installation |
| <b>Slotted or solid wall construction</b> | Use on irregularly shaped and round panel holes as well as straight paths to support a range of applications                         |
| <b>No liner to remove from adhesive</b>   | Increases productivity and lowers installed cost                                                                                     |
| <b>Available on 100' reels</b>            | Allows for easy handling and dispensing of product                                                                                   |

#### Technical Information

|                                    |                                                                                           |
|------------------------------------|-------------------------------------------------------------------------------------------|
| <b>Material:</b>                   | Polyethylene or weather resistant polyethylene with rubber based adhesive; RoHS compliant |
| <b>Maximum temperature rating:</b> | 122°F (50°C)                                                                              |
| <b>Minimum temperature rating:</b> | -40°F (-40°C)                                                                             |
| <b>Color:</b>                      | Available in natural or black (0)                                                         |
| <b>Flammability rating:</b>        | UL HB                                                                                     |


Use these tables as a guide to determine Panduit grommet edging sizes. The most common gauges for electrical applications of sheet metal dimensions are listed based on the Manufacturer Standard Gauge for Steel.

| Gauge | Manufacturer Standard Gauge for Steel (In.) |
|-------|---------------------------------------------|
| 5     | .2092                                       |
| 6     | .1943                                       |
| 7     | .1793                                       |
| 8     | .1644                                       |
| 9     | .1495                                       |
| 10    | .1345                                       |
| 11    | .1196                                       |
| 12    | .1046                                       |
| 13    | .0897                                       |


| Gauge | Manufacturer Standard Gauge for Steel (In.) |
|-------|---------------------------------------------|
| 14    | .0747                                       |
| 15    | .0673                                       |
| 16    | .0598                                       |
| 17    | .0538                                       |
| 18    | .0478                                       |
| 19    | .0418                                       |
| 20    | .0359                                       |
| 21    | .0329                                       |
| 22    | .0299                                       |

| Gauge | Manufacturer Standard Gauge for Steel (In.) |
|-------|---------------------------------------------|
| 23    | .0269                                       |
| 24    | .0239                                       |
| 25    | .0209                                       |
| 26    | .0179                                       |
| 27    | .0164                                       |
| 28    | .0149                                       |
| 29    | .0135                                       |
| 30    | .0120                                       |

# Adhesive Lined Grommet Edging



Style **GEE\_F-A-**  
Slotted Wall



Style **GES\_F-A-**  
Solid Wall

## Ordering Information

|               |                                       |         | Panel Thickness |           | Dimensions A |     | Dimensions B |     |               | Std. Pkg. Qty.* |
|---------------|---------------------------------------|---------|-----------------|-----------|--------------|-----|--------------|-----|---------------|-----------------|
| Part Number** | Material                              | Color   | In.             | mm        | In.          | mm  | In.          | mm  | Feet Per Pkg. |                 |
| Slotted Wall  |                                       |         |                 |           |              |     |              |     |               |                 |
| GEE62F-A-C    | Continuous Polyethylene with Adhesive | Natural | .036 – .062     | .9 – 1.6  | .13          | 3.3 | .16          | 4.1 | 100           | 1               |
| GEE62F-A-C0   |                                       | Black   | .036 – .062     | .9 – 1.6  | .13          | 3.3 | .16          | 4.1 | 100           | 1               |
| GEE99F-A-C    |                                       | Natural | .062 – .099     | 1.6 – 2.5 | .17          | 4.3 | .19          | 4.7 | 100           | 1               |
| GEE99F-A-C0   |                                       | Black   | .062 – .099     | 1.6 – 2.5 | .17          | 4.3 | .19          | 4.7 | 100           | 1               |
| GEE144F-A-C   |                                       | Natural | .099 – .144     | 2.5 – 3.7 | .21          | 5.4 | .22          | 5.6 | 100           | 1               |
| GEE144F-A-C0  |                                       | Black   | .099 – .144     | 2.5 – 3.7 | .21          | 5.4 | .22          | 5.6 | 100           | 1               |
| Solid Wall    |                                       |         |                 |           |              |     |              |     |               |                 |
| GES62F-A-C    | Continuous Polyethylene with Adhesive | Natural | .036 – .062     | .9 – 1.6  | .13          | 3.3 | .16          | 4.1 | 100           | 1               |
| GES62F-A-C0   |                                       | Black   | .036 – .062     | .9 – 1.6  | .13          | 3.3 | .16          | 4.1 | 100           | 1               |
| GES99F-A-C    |                                       | Natural | .062 – .099     | 1.6 – 2.5 | .17          | 4.3 | .19          | 4.7 | 100           | 1               |
| GES99F-A-C0   |                                       | Black   | .062 – .099     | 1.6 – 2.5 | .17          | 4.3 | .19          | 4.7 | 100           | 1               |
| GES144F-A-C   |                                       | Natural | .099 – .144     | 2.5 – 3.7 | .21          | 5.4 | .22          | 5.6 | 100           | 1               |
| GES144F-A-C0  |                                       | Black   | .099 – .144     | 2.5 – 3.7 | .21          | 5.4 | .22          | 5.6 | 100           | 1               |


\*Order the number of reels required.

\*\*Part numbers with “-C0” are considered weather resistant.


Reel packaging may contain splices.

## Other Grommet Edging Products Available Without Adhesive


**Nylon**  
Style **GEE\_N-**  
Slotted Wall




**Polyethylene**  
Style **GEE\_F-**  
Slotted Wall  
Also available in  
Weather Resistant  
material




**Flame Retardant Polyethylene**  
Style **GEE\_FR-**  
Slotted Wall




**Nylon and  
Flame Retardant Nylon (-69)**  
Style **GE\_-**  
Slotted Wall



**Polyethylene**  
Style **GES\_F-**  
Solid Wall  
Also available in  
Weather Resistant  
material



**Flame Retardant Polyethylene**  
Style **GES\_FR-**  
Solid Wall



### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA  
Markham, Ontario  
cs-cdn@panduit.com  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
cs-emea@panduit.com  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
cs-ap@panduit.com  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
cs-japan@panduit.com  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Jalisco, Mexico  
cs-la@panduit.com  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
cs-aus@panduit.com  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information

Visit us at [www.panduit.com](http://www.panduit.com)

Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800-777-3300 and reference WACB16

**PANDUIT®**

©2010 Panduit Corp.  
ALL RIGHTS RESERVED.  
Product Bulletin Number **WW-WACB16**  
2/2010