




φ200mm×70mm [Mass : 1800g] **9EC type**

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Airflow [m³/min] [CFM]		Max. Static Pressure [Pa] [inchH ₂ O]		SPL [dB(A)]	Operating Temperature [°C]	Expected Life [h]
9EC2024H001	24	20.4 to 26.4	2.0	48.0	3,600	11.0	388	360	1.446	60	- 20 to + 60	40,000/60℃
9EC2048J001	48	40.8 to 55.2	4.4	211.2	6,100	18.3	646	1,000	4.016	75		
9EC2048A001		43.0 to 51.0	2.2	105.6	4,800	14.7	519	640	2.570	68		
9EC2048H001		40.8 to 52.8	1.2	57.6	3,600	11.0	388	360	1.446	60		

■ Dimensions (unit: mm)




Options (unit: mm)

Finger Guards


Model : 109-720 Surface treatment : Nickel-chrome plating (silver) Color
: 109-720H : Cation electropainting (black)

Inlet side, Outlet side




Model : 109-721 Surface treatment : Nickel-chrome plating (silver) Color
: 109-721H : Cation electropainting (black)


Outlet side




Airflow - Static Pressure Characteristics



9EC2048A001



9EC2048J001



9EC2048H001

9EC2048H001

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sanyo Denki:

[9EC2048H001](#) [9EC2048A001](#) [9EC2024H001](#) [9EC2048J001](#) [9EC2024H0D01](#) [9EC2048A0D01](#)