

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

5XE17

5XE17

PAGE 1 OF 1

M

DRAWING
NUMBER

ISSUE

6

ISSUE

6

REVISIONS

A OBS DWG
CO-34416

D J D

20 DEC 74

B RE-INS
PR-4925

K P K
I APR 75

C C052067

C J H

21 SEP 82

D CO
57328-A

W J M

15 APR 85

E C094282

D L M

3 MAR 99

REPLACES

PR-4925

RELEASE NO.

CHECK

6 APR 70

EW P

6 APR 70

EW P

6 APR 70

EW P

6 APR 70

EW P

6 APR 70

EW P

6 APR 70


EW P

6 APR 70

EW P

6 APR 70

EW P



NOTE-

- 1 MOUNTING HOLES WILL ACCEPT $.087$ MAX DIA PINS OR SCREWS ON $.188 \pm .002$ CENTERS
- 2 ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- 3 WEIGHT OF SWITCH ONLY IS $.16$ OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS $.55$ OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — — — 5-17 OZ
 RELEASE FORCE — — — — — 4 OZ MIN
 RELEASE TRAVEL — — — — — $.004$ MIN
 DIFFERENTIAL TRAVEL — — — — — $.005$ MAX
 OVERTRAVEL — — — — — $.004$ MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N O

28 VOLTS DC RATING

INDUCTIVE — — — — —	SEA LEVEL — — — — —	4	AMP
	50,000 FT — — — — —	2.5	AMP
RESISTIVE — — — — —	SEA LEVEL — — — — —	7	AMP
	50,000 FT — — — — —	7	AMP
MAXIMUM INRUSH — — — — —		24	AMP

SCALE 2 TO 1

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$

WEIGHT

3

FORMTEK

FO-50378-A

DRAWN

3 APR 70

EW P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[5XE17](#)