

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200700173

Status:


Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (M12) 4 Poles, Front Panel Mount Receptacle, 1/2" - 14 NPT Threads, Female (Straight) to 22 AWG PVC Leads, 0.305m (1.0') Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Receptacles
Series	120070
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Type	Single Ended (pigtail)
UPC	78678882616
Physical	
Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	0.305m
Material - Component	Nickel-plated Zinc Die-Cast
Mounting Thread Size	1/2" - 14 NPT
Orientation	Straight
Panel Mount	Front
Poles	4
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	22
Wire/Cable Type	Leads, UL 1061
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	8R4000A18A120
Reference - Drawing Numbers	
Sales Drawing	SD-120070-016

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China RoHS

Not Reviewed

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

120070 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION