

GP Batteries


Data Sheet

Model No.: GP910A

NO MERCURY ADDED

Description : Mercury Free Alkaline Cylindrical Cell
Nominal Voltage : 1.5 Volts
Nominal Dimensions: $\varnothing 12.0$ mm x 30.2 mm
Applications : Hearing aid, pager, etc.
Average Weight : 9g
Shelf Life : Not less than 90% of the service capacity, following 1st year storage at 20°C.
Date Code : Unless otherwise specified, each cell will carry a 3 years expiry date code at the format (MM-YY), 01-04 represents the production of January 2001.
Nominal Service Life: 11.8 hrs (at 20 Ω Load to 0.9V at 20°C)

Typical Discharge Characteristics at 20°C



Close circuit voltage : 1.25 Volts (min.)(load resistor 6 Ω at 20°C for 0.3 second)

Cross References:

IEC/JIS	ANSI	Duracell	Panasonic	Varta	Others
LR1	910A	MN9100	AM5	4001	N-size, E90

