







LOC		DIST		REVISIONS				
DY	-	P	LTR	DESCRIPTION		DATE	OWN	APVD
		P		REVISED PER ECO-11-005139	19MAR11	RK	HMR	





DETAIL D
6 PIN FACE

- RECEPTACLE CONTACTS: COPPER ALLOY.
RECEPTACLE SHIELD: COPPER ALLOY.
HOUSING: THERMOPLASTIC, BLACK, 94V-0 RATED.
- PLATING:
RECEPTACLE CONTACTS - GOLD FLASH PLATED ON MATING END, MATTE-TIN PLATED .0030 MIN [.000120 MIN] THICK ON SOLDER TAIL ALL OVER .0013 MIN [.000050 MIN] THICK NICKEL.
- PLATING:
SHIELD: PRE-TIN PLATED
4. RECEPTACLE ASSEMBLY MATES WITH 6 PIN 9.00 ± .10 [.354 ± .004] DIAMETER PLUG.
- DATUMS AND BASIC DIMENSION SUPPLIED BY CUSTOMER.



6 PIN PCB LAYOUT
BOTTOM VIEW



DETAIL C
SCALE 50:1

P/N: 5749265-1 AS SHOWN

DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWG WYLEE 04JAN2005		REV SF LEONG	
9 PLC 1 PLC 2 PLC 3 PLC 4 PLC 5 PLC 6 PLC		± ± ± ± ± ± ±		NAME RECEPTACLE ASSY, 6 POS., RIGHT ANGLE, MINIATURE CIRCULAR DIN		SIZE A1	
MATERIAL		FINISH		CAGE CODE 00779		DRAWING NO 5749265	
CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1		REV P	