


1. SUGGESTED MOUNTING HOLE Ø.173 [Ø4.39]
2. HARDWARE IS INCLUDED
3. MAXIMUM MOUNTING TORQUE: 4 IN-LBS
4. THIS IS A LEAD FREE PRODUCT
5. MAXIMUM REFLOW IS 245°C FOR 5 SECONDS



BUSHING FINISH	SILVER
LEAD FINISH	SILVER
CAPACITANCE	5000pF GMV
TEMP. RANGE	-55°C TO +125°C
CURRENT	10 AMPS
WORKING VOLTAGE	85°C 100 VDC 125°C 70 VDC
DC RESISTANCE	.01 OHMS MAX.

MHz	10	100	1GHz
-----	----	-----	------

dB	20	65	70
----	----	----	----

PART: F054 M (MEXICO)
F054 (FAIRVIEW)

BAG:
1250F-054
DATE CODE
QTY./BAG (200 MAX.)

[illegible]

Quality Products From The Specialists In Electro-Magnetic Compatibility