


## 559/560 Series Fuse Holders for TE5/TR5 Type Fuses




### Dimensions units in mm

#### 559 Series



#### 560 Series



### Product Characteristics

	559 Series (Lead Free)	560 Series
Compatible Fuses	TR5/TE5	TR5/TE5
Materials	<b>Holder:</b> Black Thermoplastic, UL94 V-0 Polyamide PA 6.6 <b>Metal Parts:</b> Copper alloy; solderable tinned	
Electrical Data (23°C)	<b>Rated Voltage:</b> 250V <b>Max. Current/Power:</b> 6.3 A /1.6 W	
Mounting	PC Board, 7.18 mm pin spacing	PC Board, 5.08 mm pin spacing
Solderability	max. 260 °C, 10 s (Wave)	
Minimum Cross Section	Conducting path - 0.1 mm <sup>2</sup>	
Unit Weight	0.63 g	0,4 g

Note: Ensure proper fuseholder de-rating.

### Ordering Information

Ordering Number	"A" Height Options	Packaging
<b>559 0000 00 01</b>	6.5 mm (code 0001)	1000 Pcs Bulk
<b>559 0000 80 11</b>	10 mm (code 8011)	100 Pcs Bulk
<b>560 0000 13 19</b> <sup>1</sup>	3.0 mm (code 1319)	500 Pcs Bulk
<b>560 0000 10 09</b> <sup>1</sup>	4.3 mm (code 1009)	1000 Pcs Bulk
<b>560 0000 10 19</b> <sup>1</sup>	4.3 mm (code 1019)	500 Pcs Bulk

1. UL Recognized.

### Additional Information



**Datasheet**  
**559 Series**



**Resources**  
**559 Series**



**Samples**  
**559 Series**



**Datasheet**  
**560 Series**



**Resources**  
**560 Series**



**Samples**  
**560 Series**