


Test probes

MICRO-PRUEF MPS 2 0,64 FT



Product	MICRO-PRUEF MPS 2 0,64 FT
description	Miniature test probe with sprung stainless steel probe tip for sampling extremely small measuring points and SMD components. Because the probe tip is sprung, it cannot slip off and provides constant pressure. Connects with MKL 0,64/25-0,25 and MAL N 4-0,64/100-0,25.
operating instruction	BA003
article-no. / *colour	9739951xx  00 black  01 red
drawing	
technical data	
connection	unsprung pin Ø 0.64 mm
rated voltage ⁽¹⁾	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽³⁾
rated current ⁽¹⁾ (consider derating curve)	1 A
material socket	tip: stainless steel-BR-pin: brass
housing material	PBT
temperature range acc. To IEC61010 ⁽²⁾	-25 °C to +70 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB
standard	IEC 61010

0.64 mm system

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

⁽³⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 19.06.2019