

T-3 1/4 Miniature Bayonet Base



| Part Number | Design Voltage | Amps | MSCP | Life Hours | Filament Type |
|-------------|----------------|------|------|------------|---------------|
| CM49 | 2.00 | .06 | .04 | 1,000 | S-2 |
| CM1809 | 2.00 | .06 | .02 | 1,000 | C-6 |
| CM43 | 2.50 | .50 | .50 | 3,000 | C-2R |
| CM45 | 3.20 | .35 | .50 | 3,000 | C-2R |
| CM1490 | 3.20 | .16 | .20 | 3,000 | C-2R |
| CM1688 | 3.75 | .09 | .18 | 1,000 | C-2R |
| CM1804 | 4.00 | .06 | .07 | 1,000 | S-2 |
| CM1867 | 4.00 | .06 | .06 | 2,000 | C-6 |
| CM1850 | 5.00 | .09 | .25 | 1,500 | C-2R |
| CM1851 | 5.00 | .12 | .40 | 40 | C-2R |
| CM1906 | 5.00 | .07 | .19 | 1,000 | C-6 |
| CM316 | 6.00 | .70 | 3.40 | 500 | C-2R |
| CM1689 | 6.00 | .14 | .35 | 2,000 | C-2V |
| CM44 | 6.30 | .25 | .90 | 3,000 | C-2R |
| CM47 | 6.30 | .15 | .50 | 3,000 | C-2R |
| CM238 | 6.30 | .50 | 2.00 | 2,000 | C-2R |
| CM239 | 6.30 | .36 | .67 | 5,000 | C-2R |
| CM240 | 6.30 | .36 | .67 | 5,000 | C-2R |
| CM267 | 6.30 | .15 | .33 | 5,000 | C-2R |
| CM755 | 6.30 | .15 | .33 | 20,000 | C-2R |
| CM1302 | 6.30 | .04 | .08 | 5,000 | C-6 |
| CM1810 | 6.30 | .40 | 1.40 | 3,000 | C-2R |
| CM1847 | 6.30 | .15 | .38 | 5,000 | C-2R |
| CM1866 | 6.30 | .25 | .65 | 5,000 | C-2R |
| CM1888 | 7.00 | .50 | 2.00 | 1,500 | C-2R |
| CM1908 | 7.00 | .19 | .30 | 2,000 | C-2R |
| CM1816 | 13.0 | .33 | 3.00 | 1,000 | C-2V |
| CM181 | 14.0 | .41 | 3.00 | 1,500 | C-2F |
| CM756 | 14.0 | .08 | .31 | 15,000 | C-2F |
| CM1488 | 14.0 | .15 | 1.50 | 200 | C-2V |
| CM1815 | 14.0 | .20 | 1.40 | 3,000 | C-2V |
| CM1889 | 14.0 | .27 | 2.00 | 1,500 | C-2F |
| CM1891 | 14.0 | .24 | 2.00 | 500 | C-2F |
| CM1893 | 14.0 | .33 | 2.00 | 7,500 | C-2F |
| CM1894 | 14.0 | .24 | 2.00 | 500 | C-2V |
| CM1898 | 14.0 | .24 | 2.00 | 7,500 | 2C-2R |
| CM216 | 14.4 | .24 | 1.00 | 3,000 | C-2F |
| CM1813 | 14.4 | .10 | .86 | 1,000 | C-2V |
| CM1892 | 14.4 | .12 | .75 | 1,000 | C-2F |
| CM1909 | 14.4 | .10 | .86 | 1,000 | C-2V |
| CM1881 | 15.5 | .24 | 2.20 | 500 | C-2F |