

MNX ABS 125/50 LT



Order symbol: ABS 125/50 LT
Product nbr: 6082908
Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN: 6418074014078
El. number:
 Finland 3420604
 Denmark 8212023657
 Italy 7362043

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:		L	W	H	Rating:
mm:		130	130	50	Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes Flammability Rating (UL 746 C 5): UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 4, 4X, 6 Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 07
inch:		5.1	5.1	2	
Materials:					
Material:	ABS				
Gasket material:	TPE				
Base colour:	RAL 7035				
Cover colour:	Grey				
Cover screws material:	Polyamide				
Cover screws colour:	Black				
Temperatures:					
Short term:	-40 ... 80 °C				
Continuous:	-40 ... 60 °C				
Short term:	-40 ... 175 °F				
Continuous:	-40 ... 140 °F				
Accessories:					
MIV 125	Mounting plate (Galvanized steel)				
MIN 10	DIN-15 Mounting rail				
MIV 10	DIN-35 Mounting rail				
FP A 125/130	Front plate (Aluminium)				
HFP 130	Front plate hinge series (2 pcs)				
FP 22046	Wall fastening lug (4 pcs)				

