

## Cable Ties


### Heavy Duty Cable Ties T250 Series

These cable ties offer a high minimum tensile strength and have a buckle feature which allows the end of the cable tie to be tucked away if necessary. The buckle also snaps into HellermannTyton LTM, lashing tie mounts.



T250 heavy duty cable tie and lashing tie mount application

| Material Data         |                                                        |
|-----------------------|--------------------------------------------------------|
| Material              | <b>Polyamide 6.6 (PA66)</b>                            |
| Operating Temperature | <b>-40 °F to +185 °F (-40 °C to +85 °C) continuous</b> |
| Flammability          | <b>UL94 V2</b>                                         |



**US**  
File# E64139

| Product Selection |                  |        | Min. Tensile Strength |        | Length (L) |        | Max. Ø Bundle |       | Width (W) |        | Color   | Pkg. Qty. |
|-------------------|------------------|--------|-----------------------|--------|------------|--------|---------------|-------|-----------|--------|---------|-----------|
| Article No.       | Part No.         | Type   |                       |        |            |        |               |       |           |        |         |           |
|                   |                  |        | lbs.                  | (N)    | in.        | (mm)   | in.           | (mm)  | in.       | (mm)   |         |           |
| <b>T250S</b>      |                  |        |                       |        |            |        |               |       |           |        |         |           |
| 111-24702         | <b>T250S9X2</b>  | T250S  | 250 lbs               | (1115) | 9.05"      | (230)  | 2.17"         | (55)  | .49"      | (12.5) | Natural | 25        |
| 111-24700         | <b>T250S0X2</b>  | T250S  | 250 lbs               | (1115) | 9.05"      | (230)  | 2.17"         | (55)  | .49"      | (12.5) | Black   | 25        |
| <b>T250R</b>      |                  |        |                       |        |            |        |               |       |           |        |         |           |
| 111-24803         | <b>T250R9X2</b>  | T250R  | 250 lbs               | (1115) | 20.47"     | (520)  | 5.71"         | (145) | .49"      | (12.5) | Natural | 25        |
| 111-24801         | <b>T250R0X2</b>  | T250R  | 250 lbs               | (1115) | 20.47"     | (520)  | 5.71"         | (145) | .49"      | (12.5) | Black   | 25        |
| <b>T250M</b>      |                  |        |                       |        |            |        |               |       |           |        |         |           |
| 111-25002         | <b>T250M9X2</b>  | T250M  | 250 lbs               | (1115) | 22.24"     | (565)  | 5.90"         | (150) | .49"      | (12.5) | Natural | 25        |
| 111-25001         | <b>T250M0X2</b>  | T250M  | 250 lbs               | (1115) | 22.24"     | (565)  | 5.90"         | (150) | .49"      | (12.5) | Black   | 25        |
| <b>T250I</b>      |                  |        |                       |        |            |        |               |       |           |        |         |           |
| 111-25219         | <b>T250I9X2</b>  | T250I  | 250 lbs               | (1115) | 28.54"     | (725)  | 8.00"         | (203) | .49"      | (12.5) | Natural | 25        |
| 111-00507         | <b>T250I0X2</b>  | T250I  | 250 lbs               | (1115) | 28.54"     | (725)  | 8.00"         | (203) | .49"      | (12.5) | Black   | 25        |
| <b>T250L</b>      |                  |        |                       |        |            |        |               |       |           |        |         |           |
| 111-00436         | <b>T250L9X2</b>  | T250L  | 250 lbs               | (1115) | 34.65"     | (880)  | 10.00"        | (254) | .49"      | (12.5) | Natural | 25        |
| 111-24601         | <b>T250L0X2</b>  | T250L  | 250 lbs               | (1115) | 34.65"     | (880)  | 10.00"        | (254) | .49"      | (12.5) | Black   | 25        |
| <b>T250XL</b>     |                  |        |                       |        |            |        |               |       |           |        |         |           |
| 111-00466         | <b>T250XL9X2</b> | T250XL | 250 lbs               | (1115) | 40.55"     | (1030) | 12.00"        | (305) | .49"      | (12.5) | Natural | 25        |
| 111-25200         | <b>T250XL0X2</b> | T250XL | 250 lbs               | (1115) | 40.55"     | (1030) | 12.00"        | (305) | .49"      | (12.5) | Black   | 25        |

Installation tools - MK9, MK9HT, MK9P. Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.