



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
▶ 0,64 mm system
▶ 2 mm system
▶ 2 mm Sicherheitssystem
▶ 4 mm system
▶ 4 mm sliding sleeve system
▶ 4 mm safety system
oscilloscope test probes
measuring leads
plugs
sockets
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ test probes ▶ test probes ▶ PRUEF 2600

PRUEF 2600

datasheet for PRUEF 2600
article number: 972317101



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 972 317-101
description:	Test probe with shatter-proof insulating sleeve and slender stainless steel tip. Tip for penetration of insulation and oxide layers. 4 mm diameter brass socket connection. Connects with safety measuring leads.
typ:	PRUEF 2600 rot / red
system:	4mm safety system
order number:	972 317-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT III
pin dimensions	2 mm
type of contact:	test tip (unsprung)
type of termination:	4 mm socket (unsprung)
rated voltage:	AC/DC 1000 V
rated current:	1 A
Please consider derating curve!	
contact resistance:	50 mOhm
material	
contact material:	tip: stainless steel socket: brass
contact surface material:	nickel
housing material:	PP
environmental conditions:	
temperature range:	-25 °C to +80 °C
inflammable class:	
housing (basic material):	UL 94 HB
drawing	
	