





LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			Y	REV PER ECO 15-016064	11-9-15	CT	CD



AMP P/N 206071-1
GSFC P/N G-08-S1

	.120 [3.05]	CI-2A-019-004V-001	1-206505-4	1-206505-4
	.120 [3.05]	570566-5	1-206505-3	1-206505-3
	.120 [3.05]	LMSC 1621480-006	1-206505-2	1-206505-2
	.120 [3.05]	LMSC 1621480-006	1-206505-1	1-206505-1
	.120 [3.05]	311P407-5S-B-12	206505-4	1-206505-0
	.120 [3.05]	20025720P1078S	206505-9	206505-9
	.120 [3.05]	R4383P78S	206505-8	206505-8
	.154 [3.91]		206505-7	206505-7
	.120 [3.05]	R4383P78S-2	206505-6	206505-6
	.120 [3.05]	SC81D139-045	206505-5	206505-5
	.120 [3.05]	311P407-5S-B-12	206505-4	206505-4
	.154 [3.91]		206505-3	206505-3
	.120 [3.05]	R9259P78S	206505-2	206505-2
	.154 [3.91]	311P407-5S-B-15	206505-1	206505-1
REMARKS	DIA A	CUSTOMER P/N ON CONNECTOR	AMP P/N ON CONNECTOR	AMP P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 12-16-88 M. CLOUSER CHK. 1-24-89 T. CANTLIN APD 1-25-89		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± .— 1 PLC ± .— 2 PLC ± .005 [0.13] 3 PLC ± .— 4 PLCS ± .— ANGLES FINISH		NAME AMPLIMITE NONMAGNETIC RECEPTACLE ASSEMBLY, SERIES 90, SHELL SIZE 5, 78 POSITION	
MATERIAL SEE CALLOUTS		APPLICATION SPEC — WEIGHT —		SIZE CAGE CODE DRAWING NO A1 00779 C=206505	
SEE CALLOUTS		CUSTOMER DRAWING		RESTRICTED TO SCALE 4:1 SHEET 1 OF 1 REV Y	