

MICRO SWITCH


FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

10BS217



NOTE -

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX ON 1.000 ± .002 CENTERS
- 2 -DIAL WHEEL IS SHOWN AT THE MAX SETTING OF BREAK DISTANCE
- 3 -DIAL WHEEL ROTATION 300°

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS

AT MIN SETTING
OPERATING FORCE - - - - - 11-20 OZ
RELEASE FORCE - - - - - 10 OZ MIN
DIFFERENTIAL TRAVEL - - - .0015-.0025

AT MAX SETTING
DIFFERENTIAL TRAVEL - - - - .007 MIN
OVERTRAVEL - - - - - .010 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L17

20A 125, 250 OR 480 VAC
3/4 HP 125 VAC, 1 1/2 HP 250 VAC



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04	X	0.8/.03
ONE PLACE	X,X	0.4/.018	X,X	0.38/.015
TWO PLACES	X,X,X	0.15/.008	X,X,X	0.13/.005
THREE PLACES	X,X,X,X		X,X,X,X	
ANGLES				

DESIGN UNITS ☐ SI METRIC

☒ US CUSTOMARY

WEIGHT

10BS217

M

DRAWING
NUMBER

ISSUE

REVISIONS

A C080053
JALA
5 APR 95

RELEASE NO. PR - 5433
CHECK
CHECK
8 JAN 76
LSD
CHECK
JAN 76
K SW 7 JAN 76

FORMTEK