

900 Watt Output Switching Mode DC Power Supply



Remote Control Operation

For output power on/off and voltage/current adjustment

Features:

- Remote Control functionality allows you to turn the power on/off without turning the power switch of the unit on/off and to adjust output voltage and current without turning the dials
- Constant Voltage and Current with high load/line regulation and low noise/ripple
- 10-turn potentiometers provide precise output voltage and current control
- Remote sensing for applications that require precise voltage at the point of application
- Dual 4-digit LED displays
- Output overvoltage protection
- Overload, over-temperature, and short circuit protection
- Complete with remote control plug and power cord



Specifications	Range
Output Voltage (Res.)	1 to 30V (10mV)
Output Current (Res.)	1 to 30A (10mA)
Basic accuracy	±(0.5%+2 digits)
Load Voltage Regulation	0.1% + 5mV
Line Voltage Regulation	0.05% + 3mV
Load Current Regulation	0.2% + 5mA
Line Current Regulation	0.1% + 5mA
Ripple and Noise	<5mVrms
Power	100 to 240VAC, 50/60Hz
Dimensions	9.3 x 3.8 x 13.4" (235 x 95 x 340mm)
Weight	13.21lbs (6kg)

Ordering Information:

382290900 Watt Switching Mode DC Power Supply

