

12V Flexiprint

high bright

Specifications

Voltage	12V
Current	4.125 A
Wattage	19.8 W/m
Number of LED's	225 pcs
Length of Stripe	2.5m
Operating Temperature	-25°~+60°C
Storage Temperature	-40°~+80°C
Viewing angle	110°




Benefits

Adhesive tape on backside
RoHS compliant

Electrical and Optical Characteristics (Ta=25°C)

Part Number	Colour	Wavelength	Intensity lm
FP4-N01B-250	● warmwhite	3000-3500 °K	3600
FP4-S01B-250	● naturalwhite	4000-5000 °K	3650
FP4-W01B-250	○ white	6000-7000 °K	3650

Dimensions



Thickness: 2.0 mm

1. All specifications according to information from our manufacturers, without additional guarantee on our part
2. All dimensions are in millimetres
3. Tolerance is ± 0.2 mm unless otherwise specified
4. Specifications are subject to change without notice