



Item # LC1D150B7, TeSys D IEC Contactor - 150A - Vac Coil

TeSys D IEC Contactor - 150A - 24Vac Coil

Specifications

Termination Method	Screw Clamp
Contact Rating	600V / 150A
Coil Voltage	24Vac 50/60 Hz
50/60 Hz Voltage Code	B7
Coil Consumption Inrush	280 - 350 VA
Coil Consumption Sealed	2 - 18 VA
Power Wire Size	#8 AWG - 250MCM
Power Terminal Torque	100 lb-in (12 Nm)
Control Wire Size	#14 - #18 AWG
Control Terminal Torque	10 lb-in (1.2 Nm)
Mounting Hardware	2 x 35mm DIN Rail, M6 screw
Weight	2.5 lb (1.13 kg)
AC1 Resistive Rating	200 Amp
AC3 Inductive Rating	150 Amp
AC3 Single Phase 115V	N/A
AC3 Single Phase 230V	N/A
AC3 Three Phase 200V	40 HP
AC3 Three Phase 230V	50 HP
AC3 Three Phase 460V	100 HP
AC3 Three Phase 575V	125 HP
Control Contact Rating (1NC/0NO)	A600
UL File/CCN	E164862 / NLDX
CSA File	LR43364 3211 04
Meets Standard	IEC 60647-4
CE	Yes
RoHS	Yes