



» Search

» Advanced Search

You are here: [Connector](#) » [DIN 41612](#) » DIN female, type M, 60 pins, 4 special c...

DIN FEMALE, TYPE M, 60 PINS, 4 SPECIAL CONTACTS

Item number: 354111



DIN female, type M, 60 pins, 4 special contacts
ADD ARTICLE TO THE SHOPPING CART

Availability

Quantity: » [Add to the shopping cart](#)

Technical data

Downloads

Accessories and counter-connectors

Technical data

Designation	Value
pitch	2.54 mm
signal pins	60
type	M
termination type	Solder
loaded rows	3
version	vertical
performance level	2
RoHS	

- » Connector
 - MicroCon 0,8 mm [INTERact](#)
 - MicroStac 0.8 mm [INTERact](#)
 - MicroSpeed 1.0 mm [INTERact](#)
 - SMC 1,27 mm [INTERact](#)
 - MiniBridge 1.27 mm [INTERact](#)
 - MaxiBridge 2.54 mm [INTERact](#)
 - ERmet HM 2.0 mm
 - ERmet High Speed 2.5 mm
 - DIN 41612**
 - type B
 - type B/2
 - type B/3
 - type C
 - type C/2
 - type C/3
 - type cd
 - type D
 - type E
 - type F
 - type H11
 - type H15
 - type M
 - type R
 - type R/2
 - type R/3
 - type Q
 - type Q/2
 - type Q/3
 - PowerElements
 - Power Taps
 - D-Sub
 - Modular Jacks
 - ERbic Fieldbus Plug
 - M8/M12 Circular Connector
 - USB / Firewire
 - Terminals
 - DIL IC Sockets
 - DC-Sockets
 - Accessory
- » Housing
- » Cable
- » Designer Kits
- » Assembly Service
- » Service
- » Contact
- » Events
- » Sitemap
- » Shipping Costs



Shopping Cart

Login

Your shopping cart contains no articles.

» [Show shopping cart](#)

Direct Order

Quantity Item number

» [Add to the shopping cart](#)

Last viewed articles



[354111](#)
[DIN female, typ...](#)

Cookie Usage

In order to provide you with an optimal website and so that we can continually improve it, we use cookies. By continuing to use this website, you consent to our use of cookies. More information about cookies is available in our [privacy policy](#) / [Imprint](#).

OK