

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300100798

Status:


Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change A-Size Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 16 AWG, PVC Cable, 5.0m (16.40') Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
General	
Product Family	Industrial Cordsets
Series	130010
Connector End A	Mini-Change
Connector End B	Mini-Change
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Mini-Change Connectors
Product Name	Mini-Change
Protocol	DeviceNet
Region	America
Type	Double Ended
UPC	78678846795
Physical	
Cable Diameter	11.18mm (.440")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	16
Wire/Cable Type	STOOW
Electrical	
Current - Maximum per Contact	10.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	114030A38M050
Reference - Drawing Numbers	
Sales Drawing	SD-130010-013

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130010 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION