


Knockdown Desktop Cabinet *RCH Series*



Features

- Heavy duty, 16-gauge steel, 19" rack mount - desktop rack cabinet.
- Panel rails are infinitely adjustable (front to back), round hole punched for 10-32 clip-nuts to full EIA hole centers.
- Includes two pairs of rails (for rear support of heavier equipment or shelves), rubber feet, black ABS plastic handles, a starter pack of 10-32 clip nuts & matching **1421ABK** black screws.
- Simple assembly using one bolt in each corner to lock the sides to the top and bottom (hardware included).
- Front & back lip is .585" (14 mm) so usable depth is reduced by 1.17" (30 mm).
- Tested to nearly double the suggested load rating of 800 lbs (363 kg).
- Rugged textured powder paint finish.
- Knockdown design ships unassembled for easy handling and shipping protection.
- RoHS Compliant.
- Manufactured in North America.

Gallery



Accessories

- Locking Door
- Round Hole Punched Combination Mounting Rail
- Outlet Strips

RCHS (Solid Side Panels Included)

Part No. Black	Part No. Light Gray	Overall Dimensions			Usable Mounting Dimensions				Included Clip Nuts and Screws	Shipping Weight
		Height	Width	Depth	Height	Width	Depth	Rack Units		
RCHS1900817BK1	RCHS1900817LG1	10.75	21.00	17.50	8.75	19.00	16.25	5U	8	38 lb (17.3 kg)
RCHS1901017BK1	RCHS1901017LG1	12.50	21.00	17.50	10.50	19.00	16.25	6U	16	40 lb (18.2 kg)
RCHS1901417BK1	RCHS1901417LG1	16.00	21.00	17.50	14.00	19.00	16.25	8U	16	42 lb (19.1 kg)
RCHS1901717BK1	RCHS1901717LG1	19.50	21.00	17.50	17.50	19.00	16.25	10U	16	46 lb (20.9 kg)
RCHS1902217BK1	RCHS1902217LG1	24.75	21.00	17.50	22.75	19.00	16.25	13U	16	54 lb (24.5 kg)
RCHS1902817BK1	RCHS1902817LG1	30.00	21.00	17.50	28.00	19.00	16.25	16U	16	60 lb (27.3 kg)
RCHS1901024BK1	RCHS1901024LG1	12.50	21.00	24.50	10.50	19.00	23.25	6U	16	54 lb (24.5 kg)
RCHS1901424BK1	RCHS1901424LG1	16.00	21.00	24.50	14.00	19.00	23.25	8U	16	56 lb (25.5 kg)
RCHS1901724BK1	RCHS1901724LG1	19.50	21.00	24.50	17.50	19.00	23.25	10U	16	60 lb (27.3 kg)
RCHS1902224BK1	RCHS1902224LG1	24.75	21.00	24.50	22.75	19.00	23.25	13U	16	68 lb (30.9 kg)

Part No. Black	Part No. Light Gray	Overall Dimensions			Usable Mounting Dimensions				Included Clip Nuts and Screws	Shipping Weight
		Height	Width	Depth	Height	Width	Depth	Rack Units		
RCHS1902824BK1	RCHS1902824LG1	30.00	21.00	24.50	28.00	19.00	23.25	16U	16	76 lb (35.5 kg)
RCHS1901031BK1	RCHS1901031LG1	12.50	21.00	31.50	10.50	19.00	30.25	6U	16	64 lb (29.1 kg)
RCHS1901431BK1	RCHS1901431LG1	16.00	21.00	31.50	14.00	19.00	30.25	8U	16	68 lb (30.9 kg)
RCHS1901731BK1	RCHS1901731LG1	19.50	21.00	31.50	17.50	19.00	30.25	10U	16	74 lb (33.6 kg)
RCHS1902231BK1	RCHS1902231LG1	24.75	21.00	31.50	22.75	19.00	30.25	13U	16	82 lb (37.3 kg)
RCHS1902831BK1	RCHS1902831LG1	30.00	21.00	31.50	28.00	19.00	30.25	16U	16	92 lb (41.8 kg)

RCHV (Vented Side Panels Included)

Part No. Black	Part No. Light Gray	Overall Dimensions			Usable Mounting Dimensions				Included Clip Nuts and Screws	Shipping Weight
		Height	Width	Depth	Height	Width	Depth	Rack Units		
RCHV1900817BK1	RCHV1900817LG1	10.75	21.00	17.50	8.75	19.00	16.25	5U	8	36 lb (16.4 kg)
RCHV1901017BK1	RCHV1901017LG1	12.50	21.00	17.50	10.50	19.00	16.25	6U	16	40 lb (18.2 kg)
RCHV1901417BK1	RCHV1901417LG1	16.00	21.00	17.50	14.00	19.00	16.25	8U	16	44 lb (18.2 kg)
RCHV1901717BK1	RCHV1901717LG1	19.50	21.00	17.50	17.50	19.00	16.25	10U	16	46 lb (20.9 kg)
RCHV1902217BK1	RCHV1902217LG1	24.75	21.00	17.50	22.75	19.00	16.25	13U	16	52 lb (23.6 kg)
RCHV1902817BK1	RCHV1902817LG1	30.00	21.00	17.50	28.00	19.00	16.25	16U	16	58 lb (26.4 kg)
RCHV1901024BK1	RCHV1901024LG1	12.50	21.00	24.50	10.50	19.00	23.25	6U	16	52 lb (23.6 kg)
RCHV1901424BK1	RCHV1901424LG1	16.00	21.00	24.50	14.00	19.00	23.25	8U	16	56 lb (25.5 kg)
RCHV1901724BK1	RCHV1901724LG1	19.50	21.00	24.50	17.50	19.00	23.25	10U	16	60 lb (27.3 kg)
RCHV1902224BK1	RCHV1902224LG1	24.75	21.00	24.50	22.75	19.00	23.25	13U	16	68 lb (30.9 kg)
RCHV1902824BK1	RCHV1902824LG1	30.00	21.00	24.50	28.00	19.00	23.25	16U	16	76 lb (35.5 kg)
RCHV1901031BK1	RCHV1901031LG1	12.50	21.00	31.50	10.50	19.00	30.25	6U	16	64 lb (29.1 kg)
RCHV1901431BK1	RCHV1901431LG1	16.00	21.00	31.50	14.00	19.00	30.25	8U	16	70 lb (31.8 kg)
RCHV1901731BK1	RCHV1901731LG1	19.50	21.00	31.50	17.50	19.00	30.25	10U	16	72 lb (32.7 kg)
RCHV1902231BK1	RCHV1902231LG1	24.75	21.00	31.50	22.75	19.00	30.25	13U	16	80 lb (36.4 kg)
RCHV1902831BK1	RCHV1902831LG1	30.00	21.00	31.50	28.00	19.00	30.25	16U	16	92 lb (41.8 kg)

Optional Door Kit

Part No. Black	Part No. Light Gray	Use with Cabinet Panel Height		Shipping Weight
		Rack Units	Height	
RCHD1908BK1	RCHD1908LG1	5U	8.75	5 lb (2.3 kg)
RCHD1910BK1	RCHD1910LG1	6U	10.50	5 lb (2.3 kg)
RCHD1914BK1	RCHD1914LG1	8U	14.00	6 lb (2.7 kg)
RCHD1917BK1	RCHD1917LG1	10U	17.50	7 lb (3.2 kg)
RCHD1922BK1	RCHD1922LG1	13U	22.75	9 lb (4.1 kg)
RCHD1928BK1	RCHD1928LG1	16U	28.00	12 lb (5.5 kg)

Optional Caster Kit

Part No.	Wheel Diameter	Overall Height Added to Cabinet	Hole Mounting Pattern		Quantity Included In Set	Caster with Brakes Included
			Width	Depth		
1425PHD	2.00	2.50	0.94	2.12	4	2

Data subject to change without notice

