


Spade Type Crimp Connectors



Operating Temperature: 75°C max.

Material : Copper
Terminal : PVC
Insulation : TIN

Best.-Nr.	Typ	WIRE RANGE mm²/AWG	DIMENSION								COLOR
			STUD SIZE	d2 (mm)	B (mm)	L (mm)	F (mm)	dØ(mm)	DØ(mm)	H(mm)	
				±0.2	±0.1	±0.5	±0.2	±0.2	±0.5	±0.5	
74 52 24	SV1.25-3.2	0.5~1.5mm² 22~16 AWG	M3	3.2	5.7	21.2	6.5	1.7	4.0	10.0	RED
74 52 40	SV1.25-35S		M3.5	3.7	5.7	21.2	6.5	1.7			
74 52 54	SV1.25-4S		M4	4.3	6.4	21.2	6.5	1.7			
74 52 68	SV1.25-5S		M5	5.3	8.1	21.2	6.5	1.7			
74 52 83	SV1.25-6S		M6	6.4	9.5	21.2	6.5	1.7			
74 52 98	SV2-3.2	1.5~2.5mm² 16~14 AWG	M3	3.2	5.7	21.2	6.5	2.3	4.5	10.0	BLUE
74 53 12	SV2-3.5S		M3	3.7	5.7	21.2	6.5	2.3			
73 79 32	SV2-4S		M4	4.3	6.4	21.2	6.5	2.3			
74 53 25	SV2-5S		M5	5.3	8.1	21.2	6.5	2.3			
74 53 38	SV2-6S		M6	6.4	9.5	21.2	6.5	2.3			
73 79 71	SV2-8		M8	8.4	14.0	29.0	11.5	2.3			
73 80 04	SV3.5-3	2.5~4mm² 14~12 AWG	M3	3.2	5.7	24.8	7.0	3.0	5.6	13.0	BLACK
73 80 39	SV3.5-4		M4	4.3	8.0	24.8	7.0	3.0			
73 80 74	SV3.5-5		M5	5.3	8.0	24.8	7.0	3.0			
73 81 00	SV3.5-6		M6	6.4	12.0	28.0	12.1	3.0			
74 53 52	SV5.5-3.5	4~6mm² 12~10 AWG	M3.5	3.7	8.3	25.2	7.5	3.4	6.3	13.0	YELLOW
74 53 67	SV5.5-4S		M4	4.3	8.3	25.2	7.5	3.4			
74 53 82	SV5.5-5		M5	5.3	9.0	25.2	7.5	3.4			
74 53 96	SV5.5-6S		M6	6.4	9.0	25.2	7.5	3.4			
73 81 37	SV5.5-8		M8	8.4	14.0	30.0	11.5	3.4			