

(2,00 mm) .0787"

ETMM, TLMM SERIES

ETMM-108-02-F-D-TH-LC

TLMM-125-01-L-D-SM-K

ETMM-112-02-F-D-RA

SHROUDED STRAIN RELIEF IDC HEADER

SPECIFICATIONS

For complete specifications
see www.samtec.com?ETMM
or www.samtec.com?TLMM

Insulator Material:

Black Liquid Crystal
Polymer (ETMM)

High Temp Nylon (TLMM)

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over
50µ" (1,27 µm) Ni

Current Rating:

3A per contact
@ 80°C ambient

Operating Temp Range:

-55°C to +125°C

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,13 mm) .005" max

RoHS Compliant:

Yes

Mates with:
TLSD, TCSD, TCMD

ALSO AVAILABLE

Contact Samtec for other sizes.


See STMM Series for TCSD
mates without Strain Relief.

See LTMM for shrouded header
for mating with Connector Strips.

Shrouded pins
for protection

Surface Mount,
Through-hole and
Right Angle

Optional
Locking clips



Note: Some lengths, styles
and options are non-standard,
non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM