


**General ordering data**

Order No.	9510260000
Part designation	Klippon POK 6 Ex
Version	EXI enclosure, 90 mm, 160 mm, 260 mm, glass fibre-reinforced polyester
EAN	4008190498603
Qty.	1 pc(s).

Dimensions

Fixing dimension, height	110 mm
Fixing dimension, width	240 mm
Height	90 mm
Length	160 mm
Width	260 mm

General details

Cover fixing	4 stainless steel M6 screws
Enclosure fixing	Holes 6 mm
Sealing material	Polyurethane and chloroprene
Colour	grey
Class of protection to EN 60529	IP 66
Weight	1,710 g
Ambient temperature, min.	-40 °C
Ambient temperature, max.	90 °C

Screwed cable glands top/bottom

M 12	30
M 16	24
M 20	14
M 25	5
M 32	4
M 40	3
Side of enclosure	Top / Bottom

Screwed cable glands, left/right

M12	11
M16	6
M20	4
M25	2
M32	2
M40	1
On housing side	left / right

Approvals

Approvals institutes

GOSTEX ATEX ATEX



Classifications

ETIM 2.0	EC000520
ETIM 3.0	EC000049
eClass 4.1	27-14-12-06
eClass 5.0	27-18-05-02
eClass 5.1	27-18-05-02

Similar products

Order No.	Part designation	Version
1277700000	Klippon POK 6	Housings, 90 mm, 160 mm, 260 mm, glass fibre-reinforced polyester