

Constellation® ES.3

Data Sheet

Capacity-Optimized Enterprise Hard Drive for Bulk-Data Applications

- Highest-capacity large form factor enterprise drive—up to 4TB—for demanding data growth¹
- Sixth-generation drive technology with SAS and SATA interfaces for 24x7 reliability
- Enhanced error correction, super parity and end-to-end SAS-based data integrity for accurate data storage
- Best-in-class rotational vibration tolerance ensures consistent performance.
- Improved power and cooling efficiencies with low power consumption and on-demand PowerChoice™ technology based on T10/T13 power management standards
- Multi-drive firmware maximized for enterprise RAID system availability
- Robust performance with dual processors, ramp load technology, top-cover-attached motor and humidity sensor for optimum performance in all chassis
- Self-Encrypting Drive (AES-256) with FIPS 140-2 validation and Seagate Instant Secure Erase cuts IT drive retirement costs while securely protecting data at rest.^{2,3}

Best-Fit Applications

- High-capacity RAID storage
- Mainstream enterprise external storage arrays (SAN, NAS, DAS)
- Cloud bulk data storage
- Enterprise backup and restore—D2D, virtual tape
- Centralized surveillance

¹ Seagate recommends validating your configuration with your HBA/RAID controller manufacturer to ensure full capacity capabilities.

² Self-Encrypting Drives (SED) and FIPS 140-2 Validated drives are not available in all models or countries. May require TCG-compliant host or controller support.

³ FIPS 140-2 in review. See FIPS 140-2 Level 2 Certificate at <http://csrc.nist.gov/groups/STM/cmvp/documents/140-1/1401val2011.htm#1635>



Specifications	SATA 6Gb/s			
	4TB ^{1,2}	3TB ^{1,2}	2TB ¹	1TB ¹
Standard Model Number	ST4000NM0033	ST3000NM0033	ST2000NM0033	ST1000NM0033
SED Model Number	ST4000NM0053 ³	ST3000NM0053 ³	ST2000NM0053 ³	ST1000NM0053 ³
Features				
Humidity Sensor	Yes	Yes	Yes	Yes
Super Parity	Yes	Yes	Yes	Yes
Low Halogen	Yes	Yes	Yes	Yes
PowerChoice™ Technology	Yes	Yes	Yes	Yes
Cache, Multisegmented (MB)	128	128	128	128
Reliability/Data Integrity				
Mean Time Between Failures (MTBF, hours)	1.4 million	1.4 million	1.4 million	1.4 million
Reliability Rating @ Full 24x7 Operation (AFR)	0.63%	0.63%	0.63%	0.63%
Nonrecoverable Read Errors per Bits Read	1 sector per 10E15	1 sector per 10E15	1 sector per 10E15	1 sector per 10E15
Power-On Hours per Year	8760 (24x7)	8760 (24x7)	8760 (24x7)	8760 (24x7)
Bytes per Sector	512 Native	512 Native	512 Native	512 Native
Limited Warranty (years) ⁴	5	5	5	5
Performance				
Spindle Speed (RPM)	7200	7200	7200	7200
Max. Sustained Transfer Rate OD (MB/s)	175	175	175	175
Average Latency (ms)	4.16	4.16	4.16	4.16
Interface Ports	Single	Single	Single	Single
Rotation Vibration @ 1500 Hz (rad/s ²)	12.5	12.5	12.5	12.5
Power Consumption				
Idle Power (W)	6.73	6.73	5.17	4.45
Typical Operating, Random Read (W)	11.27	11.27	9.42	8.08
Power Supply Requirements	+12V and +5V	+12V and +5V	+12V and +5V	+12V and +5V
Environmental				
Temperature, Operating (°C)	5 to 60	5 to 60	5 to 60	5 to 60
Vibration, Nonoperating: <5Hz to 500Hz (Gs)	0.25	0.25	0.25	0.25
Shock, Operating, 2ms (Read/Write) (Gs)	70/40	70/40	70/40	70/40
Shock, Nonoperating, 1ms and 2ms (Gs)	300	300	300	300
Physical				
Height (in/mm, max) ⁵	1.028/26.1	1.028/26.1	1.028/26.1	1.028/26.1
Width (in/mm, max) ⁵	4.010/101.85	4.010/101.85	4.010/101.85	4.010/101.85
Depth (in/mm, max) ⁵	5.878/147.0	5.878/147.0	5.878/147.0	5.878/147.0
Weight (lb/g)	1.543/700	1.444/655	1.400/635	1.334/605
Carton Unit Quantity	20	20	20	20
Cartons per Pallet	40	40	40	40
Cartons per Layer	8	8	8	8

¹ One gigabyte, or GB, equals one billion bytes and one terabyte equals one trillion bytes when referring to drive capacity.

² Seagate recommends validating your configuration with your HBA/RAID controller manufacturer to ensure full capacity capabilities.

³ Self-Encrypting Drives (SED) and FIPS 140-2 Validated drives are not available in all models or countries. May require TCG-compliant host or controller support.

⁴ Capacity-optimized products shipped between December 31, 2011 and June 30, 2012, have a 3-year limited warranty. Capacity-optimized products shipped before December 31, 2011 or after June 30, 2012 have a 5-year limited warranty.

⁵ These base deck dimensions conform to the Small Form Factor Standard (SFF-8201) found at www.sffcommittee.org. For connector-related dimensions, see SFF-8223.



Specifications	6Gb/s SAS			
	4TB ^{1,2}	3TB ^{1,2}	2TB ¹	1TB ¹
Standard Model Number	ST4000NM0023	ST3000NM0023	ST2000NM0023	ST1000NM0023
SED Model Number	ST4000NM0043 ³	ST3000NM0043 ³	ST2000NM0043 ³	ST1000NM0043 ³
SED-FIPS Model Number	ST4000NM0063 ^{3,4}	ST3000NM0063 ^{3,4}	ST2000NM0063 ^{3,4}	ST1000NM0063 ^{3,4}
Features				
Protection Information (T10 DIF)	Yes	Yes	Yes	Yes
Humidity Sensor	Yes	Yes	Yes	Yes
Super Parity	Yes	Yes	Yes	Yes
Low Halogen	Yes	Yes	Yes	Yes
PowerChoice™ Technology	Yes	Yes	Yes	Yes
Cache, Multisegmented (MB)	128	128	128	128
Reliability/Data Integrity				
Mean Time Between Failures (MTBF, hours)	1.4 million	1.4 million	1.4 million	1.4 million
Reliability Rating @ Full 24x7 Operation (AFR)	0.63%	0.63%	0.63%	0.63%
Nonrecoverable Read Errors per Bits Read	1 sector per 10E15	1 sector per 10E15	1 sector per 10E15	1 sector per 10E15
Power-On Hours per Year	8760	8760	8760	8760
Bytes per Sector	512, 520, 528	512, 520, 528	512, 520, 528	512, 520, 528
Limited Warranty (years) ⁵	5	5	5	5
Performance				
Spindle Speed (RPM)	7200	7200	7200	7200
Max. Sustained Transfer Rate OD (MB/s)	175	175	175	175
Average Latency (ms)	4.16	4.16	4.16	4.16
Interface Ports	Dual	Dual	Dual	Dual
Rotation Vibration @ 1500 Hz (rad/s ²)	12.5	12.5	12.5	12.5
Power Consumption				
Idle Power (W)	7.80	6.74	5.78	4.84
Typical Operating, Random Read (W)	11.86	10.72	9.59	8.93
Power Supply Requirements	+12V and +5V	+12V and +5V	+12V and +5V	+12V and +5V
Environmental				
Temperature, Operating (°C)	5 to 60	5 to 60	5 to 60	5 to 60
Vibration, Nonoperating: <5Hz to 500Hz (Gs)	0.25	0.25	0.25	0.25
Shock, Operating, 2ms (Read/Write) (Gs)	70/40	70/40	70/40	70/40
Shock, Nonoperating, 1ms and 2ms (Gs)	300	300	300	300
Physical				
Height (in/mm, max) ⁶	1.028/26.1	1.028/26.1	1.028/26.1	1.028/26.1
Width (in/mm, max) ⁶	4.010/101.85	4.010/101.85	4.010/101.85	4.010/101.85
Depth (in/mm, max) ⁶	5.878/147.0	5.878/147.0	5.878/147.0	5.878/147.0
Weight (lb/g)	1.543/700	1.444/655	1.400/635	1.334/605
Carton Unit Quantity	20	20	20	20
Cartons per Pallet	40	40	40	40
Cartons per Layer	8	8	8	8

1 One gigabyte, or GB, equals one billion bytes and one terabyte equals one trillion bytes when referring to drive capacity.

2 Seagate recommends validating your configuration with your HBA/RAID controller manufacturer to ensure full capacity capabilities.

3 Self-Encrypting Drives (SED) and FIPS 140-2 Validated drives are not available in all models or countries. May require TCG-compliant host or controller support.

4 FIPS 140-2 in review. See FIPS 140-2 Level 2 Certificate at: <http://csrc.nist.gov/groups/STM/cmvp/documents/140-1/1401val2011.htm#1635>

5 Capacity-optimized products shipped between December 31, 2011 and June 30, 2012, have a 3-year limited warranty. Capacity-optimized products shipped before December 31, 2011 or after June 30, 2012 have a 5-year limited warranty.

6 These base deck dimensions conform to the Small Form Factor Standard (SFF-8201) found at www.sffcommittee.org. For connector-related dimensions, see SFF-8223.



www.seagate.com

AMERICAS
ASIA/PACIFIC
EUROPE, MIDDLE EAST AND AFRICA

Seagate Technology LLC 10200 South De Anza Boulevard, Cupertino, California 95014, United States, 408-658-1000
Seagate Singapore International Headquarters Pte. Ltd. 7000 Ang Mo Kio Avenue 5, Singapore 569877, 65-6485-3888
Seagate Technology SAS 16-18, rue du Dôme, 92100 Boulogne-Billancourt, France, 33 1-4186 10 00

© 2012 Seagate Technology LLC. All rights reserved. Printed in USA. Seagate, Seagate Technology and the Wave logo are registered trademarks of Seagate Technology LLC in the United States and/or other countries. Constellation and PowerChoice are either trademarks or registered trademarks of Seagate Technology LLC or one of its affiliated companies in the United States and/or other countries. The FIPS logo is a certification mark of NIST, which does not imply product endorsement by NIST, the U.S., or Canadian governments. All other trademarks or registered trademarks are the property of their respective owners. When referring to drive capacity, one gigabyte, or GB, equals one billion bytes and one terabyte, or TB, equals one trillion bytes. Your computer's operating system may use a different standard of measurement and report a lower capacity. In addition, some of the listed capacity is used for formatting and other functions, and thus will not be available for data storage. Actual data rates may vary depending on operating environment and other factors. The export or re-export of hardware or software containing encryption may be regulated by the U.S. Department of Commerce, Bureau of Industry and Security (for more information, visit www.bis.doc.gov), and controlled for import and use outside of the U.S. Seagate reserves the right to change, without notice, product offerings or specifications. DS1769.1-1210US, October 2012