



SAW Filters for TV/VCR Dual Type

Frequency Characteristics(Pictuer-ch)



Part Number	Picture Frequency (fp) (MHz)	Insertion Loss (dB)	Picture Carrier (dB)	Chroma Carrier (dB)	Sound Carrier (dB)	Adjacent Sound Carrier (dB)	Adjacent Picture Carrier (dB)
SAWGS38M0VCAZ00B03	38.00 (Picture-ch)	23.0 max.(Picture-ch) /25.0dBmax.(Sound-ch)	6.0 ±1.2dB(P-ch) /28.0dB min.(S-ch)	1.7 max.(P-ch) /30.0dBmin.(S-ch)	29.0 min. (P-ch)/-	43.0 min.(P-ch) /35.0dBmin.(S-ch)	40.0 min.(P-ch) /27.0dBmin.(S-ch)
SAWGS45M7VCFZ00B03	45.75 (Picture-ch)	21.0 max.(Picture-ch) /29.0dB max.(Sound-ch)	5.0 ±1.2dB(Picture-ch) /17.0dB min.(Sound-ch)	2.6 ±1.2dB(Picture-ch) /16.0dB min.(Sound-ch)	18.0 min. (Picture-ch)/-	40.0 min.(Picture-ch) /20.0dB min.(Sound-ch)	42.0 min.(Picture-ch) /20.0dB min.(Sound-ch)
SAWGS45M7VCGZ00B03	45.75 (Picture-ch)	23.0 max.(Picture-ch) /29.5dB max.(Sound-ch)	6.3 ±1.2dB(Picture-ch) /18.0dB min.(Sound-ch)	1.5 max.(Picture-ch) /16.0dB min.(Sound-ch)	18.0 min. (Picture-ch)/-	44.0 min.(Picture-ch) /20.0dB min.(Sound-ch)	45.0 min.(Picture-ch) /22.0dB min.(Sound-ch)
SAWGS45M7VCHZ00B03	45.75 (Picture-ch)	23.0 max.(Picture-ch) /29.5dB max.(Sound-ch)	4.6 ±1.2dB(Picture-ch) /16.0dB min.(Sound-ch)	1.7 max.(Picture-ch) /16.0dB min.(Sound-ch)	25.0 min. (Picture-ch)/-	44.0 min.(Picture-ch) /18.0dB min.(Sound-ch)	45.0 min.(Picture-ch) /21.0dB min.(Sound-ch)
SAWGS58M7VCGZ00B03	58.75 (Picture-ch)	21.0 max.(Picture-ch) /29.5dB max.(Sound-ch)	5.2 ±1.2dB(Picture-ch) /18.0dB min.(Sound-ch)	1.5 max.(Picture-ch) /16.0dBmin.(Sound-ch)	22.0 min. (Picture-ch)/-	40.0 min.(Picture-ch) /22.0dB min.(Sound-ch)	40.0 min.(Picture-ch) /22.0dB min.(Sound-ch)
SAWGS58M7VCHZ00B03	58.75 (Picture-ch)	21.0 max.(Picture-ch) /28.0dB max.(Sound-ch)	5.5 ±1.2dB(Picture-ch) /20.0dB min.(Sound-ch)	1.5 max.(Picture-ch) /12.0dBmin.(Sound-ch)	18.0 min. (Picture-ch)/-	42.0 min.(Picture-ch) /22.0dB min.(Sound-ch)	43.0 min.(Picture-ch) /22.0dB min.(Sound-ch)
SAWGS58M7VCJZ00B03	58.75 (Picture-ch)	21.0 max.(Picture-ch) /28.0dB max.(Sound-ch)	6.3 ±1.2dB(Picture-ch) /22.0dB min.(Sound-ch)	1.5 max.(Picture-ch) /15.0dBmin.(Sound-ch)	18.0 min. (Picture-ch)/-	44.0 min.(Picture-ch) /25.0dB min.(Sound-ch)	43.0 min.(Picture-ch) /25.0dB min.(Sound-ch)
SAWGS58M7VCPZ00B03	58.75 (Picture-ch)	21.0 max.(Picture-ch) /28.0dB max.(Sound-ch)	6.3 ±1.2dB(Picture-ch) /22.0dB min.(Sound-ch)	1.5 max.(Picture-ch) /15.0dBmin.(Sound-ch)	18.0 min. (Picture-ch)/-	44.0 min.(Picture-ch) /25.0dB min.(Sound-ch)	43.0 min.(Picture-ch) /25.0dB min.(Sound-ch)
SAWKE58M7VCMZ00R02	58.75 (Picture-ch)	19.0 max.(Picture-ch) /28.0dB max.(Sound-ch)	4.0 ±1.2dB(Picture-ch) /20.0dB min.(Sound-ch)	3.5 ±1.5dB(Picture-ch) /15.0dBmin.(Sound-ch)	20.0 min. (Picture-ch)/-	40.0 min.(Picture-ch) /22.0dB min.(Sound-ch)	40.0 min.(Picture-ch) /22.0dB min.(Sound-ch)