



1		2		3		4		5		6		7		8	
插頭部件 (Plug Component)			頭部剥皮尺寸 (Plug strip dimension)			線材規格(Wire Spec.)		尾部剥皮尺寸 (Terminal roj & Strip)			尾部處理 (Terminal Component)				
顏色(Color)	零件描述(Component)	數量 (Q' ty)	內剥(Strip)	外剥(Roj)	顏色(Color)	SJT 14AWG/3C 105°C 紅色(Red) 線長: (Length) 876.3 ^{+50.8} _{-12.7}		外剥(Roj)	內剥(Strip)	顏色(Color)	顏色(Color)	零件描述(Component)	數量 (Q' ty)		
35P紅色 90A±2A Red	FM-7 (15A 250V-) (IEC 320 C14)	1	5 ⁺¹ ₀	13±1	黑/Black(L)			20±1	5 ⁺¹ ₀	黑/Black(L)	35P紅色 90A±2A Red	FM-319 (15A 250V-) (IEC 320 C19)	1		
鍍鎳 (Nickel-Plated)	電腦電源線端子 (Computer power cord terminals)	3	5 ⁺¹ ₀	13±1	白/White(N)			20±1	5 ⁺¹ ₀	白/White(N)	銅本色 (Copper)	母插端子 (Receptacle Terminals)	3		
黑色(Black)	FM-7零件式內模 (FM-7 Inner Body)	1	5 ⁺¹ ₀	15±1	綠/Green(E)			20±1	5 ⁺¹ ₀	綠/Green(E)	黑色(Black)	FM-319兩件式內模 (FM-319 Inner Body)	1		




插頭端面圖
(Dimensions of Plug Face)


Insulation Thickness 0.76 mm
Overall Diameter 3.45±0.10 mm

Copper Conductor
41/0.254±0.004 mm
Resistance 8.88
(20°C (Max), ohms/km)

Jacket Thickness 0.76 mm
Overall Diameter 9.3±0.15 mm



線材截面圖
(Wire Cross-Section)



插頭端面圖
(Dimensions of Plug Face)

包裝方式(Packing)

扎線方式 (Bulk Pack)	每 10 條一扎 Per 10 pcs/Ties
紙箱尺寸 (Carton Size)	480 X 320 X 250
包裝數量 (Packing Q'ty)	PCS
標籤(Label)	UL Detachable Label
正側事項 (Carton Print)	依客戶要求印刷 (See Purchase Order)

1. 高壓測試:1500V/1Sec <0.5mA
(Hi-Pot Test:1500v/1Sec <0.5mA)

電線印字內容 Wire Printed	使用克實 線材 四印字 (Un-Filler, Gravure)	紙箱事項標記 Shipping Mark
V E322763 (UL) SJT 14AWG(2.08mm²)x3C VW-I 105°C 300V /FT c(UL) SJT 14AWG(2.08mm²)x3C FT2 105°C 300V -LF-		
(UL) SJT 14AWG(2.08mm²)x3C VW-I 105°C 300V E77975 WONDERFUL-D		
CSA SJT 14AWG(2.08mm²)x3C FT2 105°C 300V LL43774 -F- -LF-		



SIZE:	A4
UNIT:	mm
SCALE:	1:1
PROJ.	

SIGNATURE	NAME	DATE			
APPROVED					
M.F.G. CHECKED			2011/11/25	新版發行	楊承正
Q.A. CHECKED			REV DATE	DESCRIPTION	SYMBOL
DRAWN	楊承正	2011/11/25	PART No.	800-14-24D-RE-0003F	
			DWG No.		

CUSTOMER	CnC Tech, LLC
	Industrial Cable and Connector Technology