

TYPICAL INDICATOR ORDERING EXAMPLE

P01

12

C

1

A

LAMPS

Incandescent

06	6-volt
12	12-volt
18	18-volt
24	24-volt
28	28-volt
Neon	
N	110-volt

CAP COLORS

B	White
C	Red
D	Orange
E	Yellow
*F	Green
*G	Blue

* F & G not suitable with neon.

BEZELS


1	.787" Wide
2	.937" Wide

BEZEL COLORS

A	Black
B	White
C	Red
D	Orange
E	Yellow
F	Green
G	Blue
H	Gray

DESCRIPTION FOR TYPICAL ORDERING EXAMPLE

P01-12-C-1A



LAMP CODES & SPECIFICATIONS

Incandescent & Neon Lamp for Solid and Design Caps

AT602		06	12	18	24	28	N
	Voltage V	6V	12V	18V	24V	28V	110V
	Current I	80mA	50mA	35mA	25mA	22mA	1.5mA
	MSCP	.159	.215	.398	.215	.247	NA
	Endurance Hrs	2,000 average					15,000 average
	Ambient Temp Range	-10 ~ +50°C					
T-1½ Pilot Slide Base		Recommended Resistor for Neon: 33K ohms for 110V AC 100K ohms for 220V AC					

Electrical specifications are determined at a basic temperature of 25°C.

For dimension drawings of lamps see Accessories & Hardware Index (page Y1).

If the source voltage is greater than rated voltage, a ballast resistor is required.

The ballast resistor calculation and more lamp detail are shown in the Supplement; see Supplement Index (page Z1).



CAP COLORS


B	White	D	Orange	F	Green
C	Red	E	Yellow	G	Blue

Material: Polycarbonate


Finish: Glossy

F & G not suitable for neon.



AT429




OPTIONAL BEZELS & COLORS



AT204
.787" Wide Bezel



AT9201
.937" Wide Bezel






Material: Polycarbonate Standard Finish: Glossy

Color Codes: A Black B White C Red D Orange E Yellow F Green G Blue H Gray


TYPICAL INDICATOR DIMENSIONS



P01-12-C



Without Bezel






Panel Thickness:
1.0mm ~ 4.0mm
(.039" ~ .157")


The .047" diameter hole accommodates one solid 18-gauge wire.



P01-12-C-1A



With Bezel






Panel Thickness:
1.0mm ~ 4.0mm
(.039" ~ .118")


The .047" diameter hole accommodates one solid 18-gauge wire.



P01-12-C-2A



With Large Bezel



Panel Thickness:
1.0mm ~ 4.0mm
(.039" ~ .118")

The .047" diameter hole accommodates one solid 18-gauge wire.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NKK Switches:](#)

[P01-12-C-1A-RO](#)