




THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	12	Vdc
OPERATING VOLTAGE RANGE	8 ~ 18	Vdc
RATED CURRENT (MAX)	25	mA
MINIMUM SPL @ 10 cm.	87	dBA
RESONANT FREQUENCY	400±20	Hz
TONE OR PULSE RATE	CONTINUOUS	0 PULSE PER SECOND
OPERATING TEMPERATURE	-20 ~ +60	°C
STORAGE TEMPERATURE	-30 ~ +70	°C
HOUSING MATERIAL	ABS UL-94	—
TERMINAL MATERIAL	TIN-PLATED PHOSPHOR BRONZE	—
WEIGHT	8.5	grams

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	5/3/02	
A	REVISED TO NEW TEMPLATE	5/5/04	R.W.
B	REVISED SPL & RESONANT FREQUENCY	8/04/05	B.R.
C	REVISED DIMENSION SIZE AND STYLE	11/18/05	B.R.



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN <i>RABL</i>	5/02
APPROVED <i>S.J.</i>	6/02

DO NOT SCALE DRAWING



projects®
unlimited

Dayton , Ohio

AUDIO INDICATOR
AI-227

SIZE
A

DRAWING NO.
AI-227

SCALE: N.T.S.

SHEET 1 OF 1

FILE NAME
AI-227.DWG

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AI-227](#)