


OAB220 Series



AC Centrifugal Blowers - 115, 230V
220mm x 76mm (8.66" x 3.00")



Frame	Die Cast Aluminum	<u>Operating Temperature</u> -20°C ~ +70°C	
Impeller	PA66, UL94 V-0 Plastic	<u>Storage Temperature</u> -40°C ~ +80°C	
Connection	4x Wire Leads, 22 AWG UL 1015	<u>Life Expectancy</u> 35,000 Hours (L10 at 65°C) 70,000 Hours (L10 at 25°C)	
Motor	AC Induction Motor with included Capacitor, Thermally Protected, Impedance Protected, IP54	<u>Available Options</u> Multiple Speed Windings Custom Speeds Other IP/Salt Fog Ratings	
Bearing System	Ball Bearings	<u>Recommended Accessories</u> Steel Duct Ring (DR22025D)	
Dielectric Strength	1500VAC/Min, <1mA	Weight: 4.37 lbs.	
Insulation Resistance	≥100MΩ @ 500VAC/min		

Part Number	Rated Voltage (Volts AC)	Voltage Range (Volts AC)	Frequency (Hertz)	Input Power (Watts)	Rated Current (Amps)	Rated Speed (RPM)	Max Airflow (CFM)	Noise Level (dBA)	Max Static Pressure (\"H ₂ O)
OAB220-11-1WB	115	100 ~ 130	50 / 60	82 / 115	1.60 / 1.50	2650 / 2975	498 / 555	73.4 / 75.2	1.6 / 2.1
OAB220-22-1WB	230	200 ~ 245	50 / 60	82 / 115	0.71 / 0.66	2650 / 2975	498 / 555	73.4 / 75.2	1.6 / 2.1