



ANRITSU METER

Home / Temperature probes / Model MG

[Instruments](#) |
 [Temperature probes](#) |
 [Company info](#) |
 [Contact](#) |
 [Site map](#)
[Application / Technical guide / Request catalogue](#)sales@anritsu-meter.co.jp**Model MG series**


Magnet Temperature Probes

Model MG series is for magnetic surface of temperature measurement.
The magnetic force of MG-11 is bigger than MG-21.

Typical Probes of MG seriesModel **MG-11K-TS1-ANP**Model **MG-22K-GW1-ANP**

Max.Temp.	Accuracy	Response time	Durability
250°C	±1.3°C (100°C Surface)	2.0s	A

Max.Temp.	Accuracy	Response time	Durability
400°C	±1.4°C (100°C Surface)	2.0s	A



MG-11K-TS1-ANP
 1 2 3 4 5 6
How to order**Specifications**

Accuracy	Standard type ±1.3°C Miniature type ±1.4°C
Response time	2.0s
Durability	A
Max.Temp.	Low temp. 250°C High temp. 400°C

1.Head size	-1	Standard type	
	-2	Miniature type	
2.Guard Material	1	Max Temp. 250°C	
	2	Max Temp. 400°C	
3.Thermocouple	K	Chromel-Alumel	
	E	Chromel-Constantan	
4.Cable type	-TS	For WE-*1	
	-GW	For WE-*2	
5.Cable length	1	1m	
	1.5	1.5m	
	2	2m	
	2.5	2.5m	
	--	-----	
6.plug	-ANP	P plug	
	-W	Without plug	

1.Head size

You can choice Head size as below.

**2.Guard Material**

You can choice Guard Material as below.

