



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'HSTTT112-48-5'

Your search criteria matched only one product, shown below

HSTTT112-48-5



- Applications include insulating, protecting, and color coding wires and cables
- Widest temperature range of any plastic material
- Voltage: 600V
- Shrink ratio: 2:1
- Mil Spec: AMSDTL-23053/12 Class 3
- Temperature range: -400°F to 500°F (-240°C to 260°C)
- Color: Opaque
- For dry locations
- Material: Polytetrafluroethylene (PTFE)

Part Number	HSTTT11248-5
RoHS Compliancy Status	Compliant
Part Description	Semi-rigid highly heat resistant Teflon* Heat Shrink offers widest temperature range of any heat shrink material.
Material	TFE Teflon*
Color	Milky clear
CSA Certified	No
Military Specification	AMS-DTL-23053/12 Class 3
Length (ft.)	4
Length (m)	1.2
Flammability Rating	Flame Retardant
Max. Recovered I.D. (In.)	.786
Max. Recovered I.D. (mm)	20.0
Min. Expanded I.D. (In.)	1.12
Min. Expanded I.D. (mm)	26.6
Nominal Diameter / Size	1 1/8
Nominal Recovered Wall Thickness (In.)	.025
Nominal Recovered Wall Thickness (mm)	.6
Pricing Description	Heat Shrink Thin, Teflon, 1.12"(28.6mm) Dia
Shrink Ratio	2:1
Temperature Range	-88°F to 482°F (-67°C to 250°C)
Min. Order UOM	PC
Min. Order Qty.	5
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.