




OGA DIAGONAL: 13.16 [334.34]
VA DIAGONAL: 12.39 [314.63]
PA DIAGONAL: 11.70 [297.08]



SECTION A-A
SCALE: NONE

TOP LEVEL NUMBER	US NUMBER	CHINA NUMBER	TYPE	DM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-8581-203	98-0003-2633-4	59-0000-0156-6	FEC	4.27" [108.46]	AG500	23655
17-8581-205	98-0003-2634-2	N/A	NOV	8.00" [203.20]	AG500	23655
17-8581-206	98-0003-2635-9	N/A	NOV	SEE DWG	AG500	23655
17-8581-221	98-0003-2637-5	59-0000-0158-2	SER	4.27" [108.46]	AG500	23655
17-8581-227	98-0003-2639-1	N/A	SER	8.00" [203.20]	AG500	23655
17-8581-218	98-0003-3272-0	59-0000-0157-4	USB R	4.27" [108.46]	AG500	23655
17-8581-230	98-0003-2994-0	59-0000-0159-0	HID M	8.00" [203.20]	AG500	23655

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 411±10%
HOUSING ORIENTED WITH LATCH DOWN

PINOUT
1 LR
2 LL
3 SHLD
4 UL
5 UR

UNITS	INCHES [MM]
TOLERANCE UNLESS OTHERWISE SPECIFIED	
X .XX	±.03 [.76]
.XXX	±.015 [.38]
ANGLES	±1°

3M TOUCH SYSTEMS
3M TOUCH SYSTEMS
USA
USA
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE
3M TOUCH SYSTEMS. IT IS NOT TO BE REPRODUCED
WITHOUT 3M WRITTEN PERMISSION OR USED FOR
PURPOSES OTHER THAN 3M AUTHORIZED PURPOSES.

MARKETING DRAWING
SCT32NN 12.39"

REV	DATE	CHG	BY
J	1/12	SB	
H	8/11	SB	
07	6/09	SB	

DO NOT SCALE DRAWING
SCALE 1 = 1

SIZE	DOCUMENT NO.	SHEET	REV
C	28159-MKT	1 OF 1	J