


Capacitor, film, 0.22 uF, +/-20% Tol, -40/+110C, Safety: X2, 275VAC,
 Lead Spacing=15 mm



Dimensions (mm)

ID	Dimension	Tolerance
L	18	+0.3
H	12	+0.1
T	6	+0.2
S	15	
LL	4	+2
F	0.6	+/-0.05

Specifications

Manufacturer:	KEMET
Brand:	Arcotronics
Capacitance:	0.22 uF
Temperature Range:	-40/+110C
Rated Temperature:	105C
Voltage @ rated temp:	560V
Voltage AC:	275VAC
Tolerance:	+/-20%
Body Type:	Radial Box
Construction:	Wound
Application:	Safety: X2
Dissipation Factor @ 1 kHz:	0.1%
Insulation Resistance:	100 GOhm
Maximum dVdT:	400V/us
UL_1414:	250V
UL_1283:	310V
IEC_60384-14:	275V
CSA_384-14:	275V
CQC_GBT 14472:	275V
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	1750