



Sample photo

Order symbol: PCM 200/75 T
Product nbr: 6016926
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074038319
El. number:
Finland: 3421676
Electric No. Denmark: 8212027297
Electric No. Sweden: 2535445

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
mm:	255	180	75	MIN 15	DIN-15 Mounting rail
inch:	10.0	7.1	3.0	MIN 20	DIN-15 Mounting rail
				MIV 15	DIN-35 Mounting rail
				MIV 20	DIN-35 Mounting rail
Materials:				FP A 200/180	Front plate (Aluminium)
Material:	Polycarbonate			HFP 180	Front plate hinge series
Base colour:	RAL 7035 -light grey			FP 22046	Wall fastening lug (4 pcs)
Cover screws material:	Polyamide				
Cover colour:	Smoked grey				
Cover screws colour:	Black				
Gasket material:	TPE				
Temperatures:				Rating:	
Temperature °C (short term):	-40 ... 120 °C			Ingress Protection (EN 60529): IP66/67	
Temperature °C (continuous):	-40 ... 80 °C			Impact Resistance (EN 62262): IK08	
Temperature °F (short term):	-40 ... 250 °F			Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Accessories:				UV resistance: UL 508	
MIV 200	Mounting plate (Galvanized steel)			Flammability Rating: UL 746C 5V	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
				Certificates:	
				Germanischer Lloyd (GL)	
				SGS Fimko	
				Gost R	

