

Product SKU:	C1356.18.90
Product Description:	Speaker Wire, UL Listed (Wires, Misc.) 120V max., No. of Conductors: 2, Gauge Size (AWG): 24, Conductor/Strands: 7/32, Jacket: Premium Grade PVC - Clear - 500 Ft. Spool
Product Category:	Electronics - Special Applications - Audio, Video, and Entertainment Cable - Speaker Wire - Clear

**Product Construction:**

Conductor:	• 24 through 14 AWG fully-annealed 1 bare, 1 tinned stranded copper conductor per ASTM B-174
Insulation:	• Premium grade, clear PVC • Temperature Range: -20°C to +60°C

Product Specification:

No. of Conductors:	• 2
Conductor Size (AWG):	• 24
Conductor/Strands:	• 7/32
Jacket Color:	• Clear
Standard Packaging:	• Spool • 500' Spool
Standard Package Quantity:	• 4
Approximate Carton Weight (lbs):	• 12.0
Carton Dimensions (LxWxH):	• 13.2 x 6.5 x 7.4
Carton Cube:	• 0.634

UPC #:	079407762040
Put-up:	500
SCC-14:	50079407762044
Cube:	673.992
Weight Per Unit of Measure:	.01

Product Information:

Applications:	- Lamps - Radios - Stereo systems - Not for in-wall use
Compliances:	UL Wires Misc. (UL: 120V) (not for in-wall installation)

Technical Specifications

[Unit Conversion Factors](#)

[Cable Design Equations - Balanced Pair](#)

[Insulation and Jacket Properties](#)

[Temperature Conversion Chart](#)

[Decimal and Unit Conversion Factors](#)

[Cable Design Equations - Braid Shield](#)

[AWG Conductor Chart](#)

[Conduit Capacity Chart](#)

[Cable Design Equations - Coaxial Cable](#)

[Engineering Prefixes](#)

[Coax Connector Cross Reference](#)

[Glossary](#)



**CAROL
BRAND**

