


SUBMINIATURE DH Series

Features

- Ultraminiature dimensions, just 0.323" x 0.106" x 0.244" (8.2mm x 2.7mm x 6.2mm)
- Specially designed for low switching currents and voltages
- Available with or without integrated auxiliary actuator
- Can be fitted to circuit boards in upright position or horizontally with formed terminals



Electrical Ratings

Switch Series	Electrical Rating
DH3	50 to 300mA@30VDC
DH4	5 to 50mA@30VDC

Specifications

Electrical	
Temperature Rating:	-25°C to +70°C
Flammability Rating:	UL94V-O

Materials	
Base:	PPS
Button:	PBT
Cover:	PBT
Auxiliary Actuator:	Stainless Steel
Terminals:	Silver-Plated Brass
Contacts:	Silver-Plated Brass (DH3) Gold-Plated Brass (DH4)

PBT = Polybutyleneterephthalate • PPS = Polyphenylene Sulphide



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cherry Electrical:

[DH3C-C5AA](#) [DH4C-C5AA](#) [DH3C-C6LA](#) [DH3C-C6AA](#) [DH4C-C6AA](#) [DH4C-C6LA](#) [DH4C-C5LA](#) [DH3C-C5LA](#) [DH3C-B1LA](#) [DH3C-B1AA](#) [DH4C-B1PA](#) [DH4C-B1AA](#) [DH4C-B1LA](#) [DH3C-C4LA](#) [DH4C-C4LA](#)